

POWERED BY



PMT200B-81326

DryLine® Dehydrator, Low-pressure membrane, wall mountable, 3.0 psig, with discrete alarm, 240 Vac, 50/60 Hz, includes four individually-valved output ports


- See related products for dc options, sold separately

PMT200B-81326

POWERED BY



Outline Drawing-Front




PMT200B-81326

POWERED BY



Outline Drawing-Side




PMT200B SIDE VIEW

PMT200B-81326

POWERED BY




Outline Drawing-Back



PMT200B-81326



Outline Drawing-Top



PMT200B TOP VIEW

Alarm

Alarm Type	Discrete
Excess-Run Alarm	10 minutes, factory set
High-Humidity Alarm	7.5% RH, factory set
Low-Pressure Alarm	68 mbar 7 kPa 1 psig
Power-Fail Alarm	Loss of input power

Dimensions

Net Weight	16.6 kg 36.5 lb
Product Depth	177.8 mm 7.0 in
Product Height	457.2 mm 18.0 in
Product Width	444.5 mm 17.5 in
Gross Weight, Packed	21.8 kg 48.1 lb
Product Depth, Packed	406.4 mm 16.0 in
Product Height, Packed	558.8 mm 22.0 in
Product Width, Packed	533.4 mm 21.0 in

Electrical Specifications

Power Cord	Europe power cord with stripped leads USA power cord
Voltage	240 Vac ±10%
Alarm Contact Rating	Form C dry contacts, 2 amps at 30 Vdc
Operating Temperature	-10 °C to +50 °C (+14 °F to +122 °F)

PMT200B-81326

POWERED BY



Power Consumption, average	190.0 W
Power Frequency	60/50 Hz
Power Phase	Single
Suggested Circuit Breaker Size	15 A
Circuit Breaker Requirement	Electrical connections require separate circuits for dehydrator installation

General Specifications

Dehydrator Type	Automatic Membrane
Voltage Type	ac
Volume Capacity, minimum	0.3 L 0.0 ft ³
Volume Capacity, maximum	1699.0 L 60.0 ft ³
Brand	DryLine®
Dew Point	Better than -45 °C (-50 °F) at 95% RH at +40 °C (+104 °F)
Flow Rate	5.7 SLPM 0.2 SCFM
Includes	3/8 in polyethylene tubing Drill template Instruction sheet Male connector fitting Power cord Power cord connector lock Street tee fitting Union tee
Mount Type	Floor Shelf Wall
Port Count	4
Port Type	3/8 in PE tube
Regulated Output Pressure Type	factory set
Regulated Output Pressure, maximum	34.5 kPa 5.0 psig

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
China RoHS SJ/T 11364-2006	Below Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

