



SD-003-KIT1

Static Desiccator Dehydrator, with parallel mounting accessories kit

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. Orange color when dry, turns green when saturated.

Dimensions

Net Weight	0.2 kg 0.4 lb
Product Depth	50.8 mm 2.0 in
Product Height	127.0 mm 5.0 in
Product Width	50.8 mm 2.0 in
Gross Weight, Packed	0.2 kg 0.4 lb
Product Depth, Packed	127.0 mm 5.0 in
Product Height, Packed	50.8 mm 2.0 in
Product Width, Packed	50.8 mm 2.0 in

Electrical Specifications

Operating Temperature	-29 °C to +49 °C (-20 °F to +120 °F)
-----------------------	--------------------------------------

General Specifications

Dehydrator Type	Desiccant
Volume Capacity, minimum	0.0 L 0.0 ft ³
Volume Capacity, maximum	28.3 L 1.0 ft ³
Desiccant Capacity	283 liters (10 cu ft) at 80% RH, +20 °C
Includes	90° elbow fitting Brass pipe nipple Instruction sheet Static desiccator
Mount Type	Pole
Port Count	1
Port Type	3/8 in PE tube x 1/8 NPT

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system