



SEC-638  
SnapSeal™ Entry Cushion with 6 holes for 3/8 in corrugated coaxial cable

## Dimensions

Nominal Size	3/8 in
Height	101.60 mm   4.00 in
Length	31.75 mm   1.25 in

## General Specifications

Cable Type	Corrugated
Cables per Cushion	6
Color	Black
Includes	Compression ring   SnapSeal™ entry cushion
Material Type	Thermoplastic elastomer
Package Quantity	1

## Mechanical Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.9.0   IEC 60529:2001, IP66

## Packed Dimensions

Height	169.9 mm   6.7 in
Length	99.8 mm   3.9 in
Shipping Weight	0.80 kg   1.76 lb
Width	129.8 mm   5.1 in

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system