



FM 1696
BS EN ISO 9001:2008

PRODUCT DATA

Date: January 2014

Information Sheet No.: TDS01481-01

EVO-STIK 584 SOLVENTED CONTAT ADHESIVE

EVO-STIK 584 is a single part solvented contact adhesive that has been specially developed for bonding expanded polystyrene. Easily applied **EVO-STIK 584** exhibits fast drying and has a long open time, its initial bond strength allows for immediate handling of assemblies, the resulting bonds involving cellular plastics will generally prove stronger than the cellular components themselves.

RECOMMENDED USE

EVO-STIK 584 has been developed for bonding expanded polystyrene and other rigid and semi rigid cellular plastics to themselves and many other substrates. The solvent system used has no detrimental effects on polystyrene or other expanded materials if used in accordance with the instructions given below.

EVO-STIK 584 is intended for bonding thermal insulation materials in general building construction, in cold storage installations and in refrigeration & chemical plant etc.

BONDING INSTRUCTIONS

SURFACE PREPARATION

- Substrates to be bonded should be perfectly clean dry and free from dust and grease.
- Smooth or polished surfaces should first be roughened with fine abrasive.
- If degreasing is necessary, a detergent/water treatment should first be considered. If this is inappropriate a suitable solvent e.g. cleaner 5 may be used. It is advisable to check the effects of degreasing solvents on plastics, rubber materials and painted surfaces before carrying out the operation. All traces of cleaning solvents must be allowed to evaporate completely before application of the adhesive.

APPLICATION

- **EVO-STIK 584** can be applied by brush or serrated trowel or spreader.
- Apply a thin even film of adhesive to both surfaces to be bonded. Ensure coverage is adequate, and allow to dry until all the solvent has evaporated, when the adhesive will still be sticky.

DRYING

Drying time depends on film thickness, surface porosity, temperature and humidity but is usually in the region of 15 minutes.

BONDING METHOD

- The two adhesive coated surfaces should first be carefully aligned, then brought into contact and pressed firmly together over the whole bond area.
- Apply as much pressure as possible by hand roller, static press or nip roller without causing damage. Sustained pressure is not necessary.
- Bringing the surfaces together before the surfaces are touch dry will result in solvent being trapped, adversely affecting the final bond, and possibly giving rise to blistering problems.
- The initial bond strength allows immediate handling, but maximum bond strength is reached after 2 - 3 hours at normal temperatures.

GENERAL PRECAUTIONS

- Do not add anything to the adhesive to modify its properties.

See final page for disclaimer

Bostik Limited, Ulverscroft Road, Leicester, LE4 6BW England. Tel: +44 (0)1785 272625 Fax: +44 (0)1785 272867

www.Bostik.co.uk

BOSTIK, EVO-STIK, CEMENTONE, SEALOCRETE, VALLANCE, LAYBOND, BISCEM & IDENDEN ARE REGISTERED TRADEMARKS OF BOSTIK LIMITED.

Page 1 of 2

- After each use, close the container tightly in order to avoid solvent evaporation.

TYPICAL CHARACTERISTICS

Physical Form:	Moderately viscous liquid
Colour:	Pale yellow
Chemical Type:	Synthetic rubber/resin blend
Solvent:	Aliphatic Hydrocarbon
Viscosity (Brookfield RVT, 10rpm at 25°C):	Approx. 2750 mPas
Solids Content:	Approx. 29%
Specific Gravity:	Approx. 0.76
Flammability:	Highly flammable

PACKAGING

For current pack sizes please contact the customer services department

STORAGE

Store in accordance with the requirements of the petroleum regulations in a dry flameproof area between 5 and 25°C.

SHELF LIFE

12 months in its original container stored under the above conditions

MATERIAL SAFETY DATA

For further information refer to the relevant Health and Safety Data Sheet.

Disclaimer - please read carefully

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, or its liability for fraud, or fraudulent misrepresentation, or any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Bostik Limited, Ulverscroft Road, Leicester, LE4 6BW England. Tel: +44 (0)1785 272625 Fax: +44 (0)1785 272867

www.Bostik.co.uk