



MC-RM1550-3

Universal Ring Mount, 15 in to 50 in OD

Dimensions

Mounting Diameter, maximum	1270.0 mm		50 in
Mounting Diameter, minimum	381.0 mm		15 in
Height	254.0 mm		10.0 in
Length	152.4 mm		6.0 in
Mounting Circumference, maximum	3990.3 mm		157.1 in
Mounting Circumference, minimum	1196.3 mm		47.1 in
Weight	117.9 kg		260.0 lb
Width	736.6 mm		29.0 in

Environmental Specifications

Wind Rating	140 mph (BWS) at 150 ft AGL 160 mph (3-second gust) at 150 ft AGL using Exposure D per FBC
Wind Rating Criteria	Four 72 in x 8 in panel antennas per sector
Wind Rating Test Method	TIA/EIA-222

General Specifications

Product Type	Universal ring mount
Includes	Mount Threaded rod
Material Type	Hot dip galvanized steel
Mounting	Monopole, 381–1270 mm (15–50 in) OD
Package Quantity	1
Sectors, quantity	3

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--