



CLEANER 2

SOLVENT BASED ADHESIVES

KEY FEATURES

- Thinner for polychloroprene adhesives
- Cleaner for tools & equipment
- Grease & dirt remover

DESCRIPTION

Cleaner 2 is an aromatic hydrocarbon based solvent.

RECOMMENDED USE

Cleaner 2 may be used thinning solvent-borne natural rubber, reclaimed rubber, SBR and polychloroprene adhesives to provide lower viscosities for meeting special application requirements. It may also be used for cleaning application equipment used with these adhesive types. **Cleaner 2** is suitable for removing grease and dirt from various surfaces.

IMPORTANT

Before embarking on any work involving **Cleaner 2** the safety data sheet should be carefully studied by those carrying out the work.
Please take care when opening the inner seal in the can.

TYPICAL CHARACTERISTICS

Physical form	Mobile liquid
Colour	Colourless
Chemical type	Mixture of petroleum spirit and toluene
Odour	Hydrocarbon
Flammability	Highly flammable
Flash Point (closed cup)	In the group -18°C to -7°C
Relative density	Approx. 0.88

BSI STANDARDS



METHOD OF USE

Note: A small trial should be carried out to ensure that the surfaces will not be attacked before cleaning commences

- Moisten rag or cotton wool with **Cleaner 2** and wipe the contaminated surface, avoiding surface recontamination by frequently changing the rag/cotton wool.

- Allow residual solvent to dry before carrying out subsequent operations.

PACKAGING

Please refer to Customer Service Department for current pack sizes.

STORAGE

Store in original sealed containers in a dry, well ventilated, flameproof place between 5 – 25°C.

SHELF LIFE

At least 2 years from date of manufacture, under the above conditions of storage.

Disclaimer – please read carefully

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products. This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS. This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, or its liability for fraud, or fraudulent misrepresentation, or any other liability which cannot be excluded or limited under applicable law. The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User. The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS. The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests. This TDS covers just one of a large range of products supplied by the Company. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products and users of it must ensure that it is the current issue. Destroy all previous TDSs, and if in any doubt, contact the Company, quoting the code number on the bottom right hand side of this page.

SMART HELP

Please contact your local representative



Bostik Ltd.
Stafford, UK
Phone : +44 (0) 1785 27 27 27
Fax : +44 (0) 1785 22 26 65
www.bostik.co.uk

Bostik S.A.
La Plaine Saint-Denis, France
Phone : +33 (0)1 55 99 90 00
Fax : +33 (0)1 55 99 90 01
www.bostik.fr

Bostik GmbH
Borgholzhausen, Germany
Phone : +49 (0)54 25/801-0
Fax : +49 (0)54 25/801140
www.bostik.de

Bostik B.V.
's-Hertogenbosch, The Netherlands
Phone : +31 (0)7 36 244 244
Fax : +31 (0)7 36 244 344
www.bostik.nl