

MTC9651M72

Universal Ring Mount Kit, 15 in to 50 in OD, includes pipe

Dimensions

Mounting Diameter, maximum	1270.0 mm		50 in
Mounting Diameter, minimum	381.0 mm		15 in
Pipe Outer Diameter	60.3 mm		2 3/8 in
Height	1828.8 mm		72.0 in
Length	1016.0 mm		40.0 in
Weight	249.5 kg		550.0 lb
Width	254.0 mm		10.0 in

General Specifications

Product Type	Universal ring mount		
Pipe Length	1828.8 mm		72.0 in
Pipe, quantity	3		
Includes	Pipe mounts		Ring mount Stand-off arms
Material Type	Hot dip galvanized steel		
Sectors, quantity	3		
Stand-off Distance	1016.0 mm		40.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

MT-651 — Plain End Pipe, 2-3/8 in OD x 72 in

MC-SA40-B — Stand-off Arm with U-bolts

MC-RM1550-3 — Universal Ring Mount, 15 in to 50 in OD