

## MTC9651S96

**Universal Ring Mount Kit, 10 in to 30 in OD, includes pipe**

### Dimensions

Mounting Diameter, maximum	762.0 mm		30 in
Mounting Diameter, minimum	254.0 mm		10 in
Pipe Outer Diameter	60.3 mm		2 3/8 in
Height	2438.4 mm		96.0 in
Length	1016.0 mm		40.0 in
Weight	229.1 kg		505.0 lb
Width	254.0 mm		10.0 in

### General Specifications

Product Type	Universal ring mount		
Pipe Length	2438.4 mm		96.0 in
Pipe, quantity	3		
Includes	Pipe mounts		Ring mount   Stand-off arms
Material Type	Hot dip galvanized steel		
Sectors, quantity	3		
Stand-off Distance	1016.0 mm		40.0 in

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### Included Products

- MT-651-96 — Plain End Pipe, 2-3/8 in OD x 96 in
- MC-SA40-B — Stand-off Arm with U-bolts
- MC-RM1030-3 — Universal Ring Mount, 10 in to 30 in OD