

IS-DM200



The IS-DM200 camera is a Quad-streaming, H.264 & MJPEG encoding, 2.0 Megapixel resolution, IP-addressable, network camera. It is designed to deliver full-motion, high-definition, progressive scan digital video across local area networks. The IS-DM200 features a 1/2.8" CMOS sensor, Power over Ethernet, 21 IR LED, Audio-In and Audio-Out. The IS-DM200 is a cost-effective, high-level, megapixel network camera.



Dimensions

- **Weight:** 0.62 lbs. (280 g)
- **Dimensions:** 4.6 x 3.6 in (117 x 90 mm)

Performance Specification

- **Sensor:** 2.0 MP CMOS
- **Maximum Resolution:** 1920 x 1080
- **Active Pixel Count:** 2,073,600
- **Maximum Frame Rate:** 60 FPS (at max res.)
- **Compression:** MJPEG / H.264
- **Streaming:** Quad H.264 + MJPEG
- **0.2 lux (color)** at F/1.4
- **0.02 lux (BW)** at F/1.4
- **Backlight Compensation**
- **Wide Dynamic Range**
- **Dynamic Range:** 96 dB
- **3D Noise Reduction**
- **ONVIF Profile S**

Technical Specification

- **Lens:** 3 - 10.5 mm Vari-Focal Zoom Lens
- **Two-Way Audio**
- **Micro-SD Storage**
- **Motion Detection**
- **Tamper Detection**
- **Alarm I/O**
- **UDP, TCP/IP, HTTP, TFTP, RTP/RTSP**
- **100/10 LAN Connection**
- **Security:** User name and Password

Electrical Specification

- **Power Consumption:** 12 watts (Camera: 7.5W, Lens: 2W, and IRs 2.5W)
- **Power requirement:** 12 VDC/ 24 VAC or via a 3-pin removable connector or via IEEE 802.3af Power over Ethernet on CAT-5 cable

Environmental Specification:

Operating Temperature -10 to -50 Degrees Celsius

Warranty

3 Years, Parts and Labor