

519 S.W. Park Street
Okeechobee, FL 34972
sales@ceeco.net
www.ceeco.net



Toll Free: 1-888-357-0798
Direct Tel: 1-863-357-0798
Facsimile: 1-863-357-0006

HOB OPEN ENCLOSURE TELEPHONES

331 & 333 HOB OPEN ENCLOSURE TELEPHONES

Stainless Steel telephones in an open enclosure steel housing

The CEECO HOB Series open enclosure, weather resistant telephones are designed for high vandalism areas subject to fraud and abuse. These attractive yet sturdy units are installed in a powder coated heavy duty steel or a stainless steel housing with a high grade stainless steel panel to eliminate rust and corrosion as well as easy maintenance. They are equipped with tamper resistant hardware to protect the phones from vandalism and theft as well as over-voltage protection to help guard against surging that might be generated by various conditions and weather. These phones are ideal for emergency and courtesy use in hospitals, malls, college and university campuses, warehouses, stations, and more.



Made in the USA

FEATURES

Measurements:

7 1/4"W x 11 1/2"H x 5"D

Weight 10 lbs

Powder Coated Steel or Stainless Steel Open Enclosure Housing

Stainless Steel Panel with Tamper Resistant Hardware

Marine Quality Chrome Hookswitch


Vandal Resistant Chrome Tone Dial

Hearing Aide Compatible Armored Cord Handset

Line Powered

Requires 301-064 Security Tool for Installation

1 Year Warranty and Lifetime Support



HOB-331/333 HOUSING SPECS

CEECO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEECO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. We offer support for the life of the product! CEECO is devoted to giving you the quality and service you deserve.

PROVIDING EXCELLENT PRODUCT & SERVICE YOU CAN TRUST, SINCE 1930

HOB OPEN ENCLOSURE TELEPHONES

331 & 333 HOB OPEN ENCLOSURE TELEPHONES

Stainless Steel telephones in an open enclosure steel housing

KEYPAD OPEN ENCLOSURES	AUTO DIAL OPEN ENCLOSURES	OTHER OPEN ENCLOSURES
<p>HOB-331-F HOB-333-FD-R</p>	<p>HOB-333-DD-R HOB-331-D-RIS</p>	<p>HOB-333-E HOB-331-X-M-IVC-RIL</p>
<p>Dimensions: 11 1/2"H x 7 1/4"W x 5"D</p>	<p>Dimensions: 11 1/2"H x 7 1/4"W x 5"D</p>	<p>Dimensions: 11 1/2"H x 7 1/4"W x 5"D</p>
<p>Weather Resistant Open Enclosure with Stainless steel Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset</p> <ul style="list-style-type: none"> Hearing aid compatible <p>HOB-331-F Model Chrome Tone Dial Keypad (F)</p> <ul style="list-style-type: none"> Ability to allow incoming or outgoing calls <p>HOB-333-F Model Chrome Tone Dial Keypad (F) SMART Features</p> <ul style="list-style-type: none"> Ability to allow or block incoming calls Call restriction capability Option to auto dial PBX or access numbers Programmable conversation time-out Optional speed dialing <p>HOB-333-FD Model Chrome Tone Dial Keypad (F) SMART Features and a Auto Dial Push Button (D)</p> <ul style="list-style-type: none"> Can be programmed to dial up to 25 digits Optional access code prefix dialing 	<p>Weather Resistant Open Enclosure with Stainless steel Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset</p> <ul style="list-style-type: none"> Hearing aid compatible <p>HOB-331-F Model Automatic Dialer (D)</p> <ul style="list-style-type: none"> Activated when the handset is lifted Will auto dial a single number from 1-11 digits <p>WPP-333-D Model Automatic Dialer (D) SMART Features</p> <ul style="list-style-type: none"> Can be programmed to dial up to 25 digits Optional access code prefix dialing Ability to allow or block incoming calls <p>HOB-333-DD Model Auto Dial Push Button (DD)</p> <ul style="list-style-type: none"> Two programmable auto dial buttons Ability to allow or block incoming calls 	<p>Weather Resistant Open Enclosure with Stainless steel Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset</p> <ul style="list-style-type: none"> Hearing aid compatible <p>HOB-331-X Model Ring-down Operation (X)</p> <ul style="list-style-type: none"> Activated when the handset is lifted Ability to allow incoming calls Initiate a call when programmed through a PBX or phone system <p>HOB-333-E Model 12 Button Auto Dial Keypad (E)</p> <ul style="list-style-type: none"> Each button is programmable to speed dial a single number from 1-23 digits Label area provided to list call destination next to each button Ability to allow or block incoming calls Speed dial capability only, no other calls allowed

ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-M	-IVC	-ACH**	-LB	Open Enclosure Housing	-RIL	-RIS
<p>Sealed Magnetic Hookswitch</p> <ul style="list-style-type: none"> Completely Sealed No Moving Parts 	<p>Push Button Volume Control</p> <p>Background Noise reducer</p>	<p>Other Length armored cord from 14" to 72"(inches). Example: -ACH14 14" Long</p>	<p>Handset with internal steel lanyard (braided metal rope) and lanyard mounting bracket that is secured onto panel for added strength.</p>	<p>Standard Black Housing -R Red Housing -S Stainless Steel Housing</p>	<p>Ring Indicator Light located on the phone panel for visual ring indication</p>	<p>Ring Indicator Light located on the phone panel for visual ring indication</p>

Visit our website at www.ceeco.net or call us at 863-357-0798 for detail specifications on any of our models.