

519 S.W. Park Street
Okeechobee, FL 34972
sales@ceeco.net
www.ceeco.net



Toll Free: 1-888-357-0798
Direct Tel: 1-863-357-0798
Facsimile: 1-863-357-0006

HOB OPEN ENCLOSURE SPEAKERPHONES

531 & 530 HOB OPEN ENCLOSURE SPEAKERPHONES

Stainless Steel Speakerphones in an Open Enclosure Steel Housing

CEEEO HOB-531 Series is an open enclosure, weather resistant, handsfree speakerphone that is designed for both indoor and outdoor areas offering limited protection from the elements. The speakerphone is a press to start, press to stop call button for the initiation and termination of phone calls with an LED visual call process indication light. Handsfree operation eliminates out of service complaints and costly repairs due to missing handsets. Automatic disconnect circuits ensure that the telephone will not be left in the "off-hook" position. The speakerphone can allow/disallow incoming calls as well as timed calls if desired. The telephone housing is powder coated steel or stainless steel with a high grade stainless steel panel to eliminate rust and corrosion which provides an attractive finish. The internal circuitry provides exceptional audio balancing and overall sound quality, as well as over-voltage protection to help guard against surging that might be generated by various conditions including storms. Our HOB-531 Series are built to last!



Made in the USA

SPECIFICATIONS

<u>Mounting :</u>	Open Enclosure Housing 4 holes spaced 8" x 5 7/8"
<u>Environment:</u>	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensing
<u>Input Power:</u>	Telephone Line Powered
<u>Loop Current:</u>	30mA min to 80mA max
<u>Loop Current:</u>	27mA min. to 80mA max. (low power)
<u>Impedance:</u>	600 ohms
<u>Type Jack:</u>	RJ11C
<u>Ringer Equivalency:</u>	0.4A
<u>UL & FCC Registration:</u>	Certified
<u>ACCESSORIES:</u>	301-064 Security Tool (required for installation)

FEATURES

Panel Size: 7 1/6"W x 11 1/4"H
Open Enclosure Housing: 7 1/4"W x 11 1/2"H x 5"D

Weight Approximately 10 lbs

Painted (black or red) Steel or Stainless Steel Open Enclosure Housing

Stainless Steel Faceplate with Tamper Resistant Hardware

Available with keypad, autodial, or ring-down function.


Provides programmable call restrictions and speed dial

Over-voltage protection to help guard against surging

Line Powered

Requires 301-064 Security Tool for Installation

1 Year Warranty and Lifetime Support



CEEEO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEEEO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. We offer support for the life of the product! CEEEO is devoted to giving you the quality and service you deserve.

PROVIDING EXCELLENT PRODUCT & SERVICE YOU CAN TRUST, SINCE 1930

519 S.W. Park Street
Okeechobee, FL 34972
sales@ceeco.net
www.ceeco.net






Toll Free: 1-888-357-0798
Direct Tel: 1-863-357-0798
Facsimile: 1-863-357-0006

HOB OPEN ENCLOSURE SPEAKERPHONES





531 & 530 HOB OPEN ENCLOSURE SPEAKERPHONES

Stainless Steel speakerphones in an open enclosure Housing

OPEN ENCLOSURE KEYPAD SPEAKERPHONES		OPEN ENCLOSURE AUTO DIAL SPEAKERPHONES		OPEN ENCLOSURE RING-DOWN SPEAKERPHONES	
HOB-531-F	HOB-531-FD-S	HOB-531-D or HOB-531-D2	HOB-531-DD-ADA-R	HOB-531-X	HOB-531-X-ADA
					
Dimensions: 11 1/2"H x 7 1/4"W x 5"D (top)		Dimensions: 11 1/2"H x 7 1/4"W x 5"D (top)		Dimensions: 11 1/2"H x 7 1/4"W x 5"D (top)	
<p>Weather Resistant Open Enclosure with Stainless steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Resets After Call Party Disconnect Can Accept or Block Incoming Calling</p> <p>HOB-531-F Model Chrome Dial Keypad (F)</p> <ul style="list-style-type: none"> • Ability to allow or block incoming calls • Call restriction capability • Programmable conversation time-out • Optional speed dialing • Programmable PBX prefix dialing or access number <p>HOB-531-FD Model Chrome Tone Dial Keypad (F) and Auto Dial Push Button (D)</p> <ul style="list-style-type: none"> • Ability to allow or block incoming calls • Call restriction capability • Programmable conversation time-out • Optional speed dialing • Programmable PBX prefix dialing or access number 		<p>Weather Resistant Open Enclosure with Stainless steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Resets After Call Party Disconnect Can Accept or Block Incoming Calling</p> <p>SSP-511-D Model Auto Dial Push Button (D)</p> <ul style="list-style-type: none"> • Ability to allow or block incoming calls • Programmable conversation time-out capability • Programmable PBX prefix dialing or access number <p>HOB-531-D2 Model Auto Dial Push Button (D2)</p> <ul style="list-style-type: none"> • Will dial a second number if called party doesn't answer first number dialed <p>HOB-531-DD Model Auto Dial Push Button (DD)</p> <ul style="list-style-type: none"> • Two programmable auto dial buttons • Ability to allow or block incoming calls • Programmable conversation time-out capability 		<p>Weather Resistant Open Enclosure with Stainless steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Resets After Call Party Disconnect Can Accept or Block Incoming Calling</p> <p>HOB-531-X Model Ring-down Operation (X)</p> <ul style="list-style-type: none"> • Ability to allow or block incoming calls • Initiate a call when programmed through a PBX or phone system 	
				LOW POWER MODELS	
				<p>HOB-530-F, HOB-530-D, HOB-530-X</p> <ul style="list-style-type: none"> • Full Function ADA features are NOT available 	

ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-ADA	Open Enclosure Housing	-RIS	-RIL	Additional Options & Features
				Auto Answer (AA) Voice Active (VA) Auto Answer (AA)
<ul style="list-style-type: none"> • Red/ green LED call progress indicator light • Braille Emergency Plate "EMERG. PHONE" • Red push button 	<p>Standard Black Housing</p> <p>-R Red Housing</p> <p>-S Stainless Steel Housing</p>	<p>Ring Indicator Flashing Blue Light</p> <p>(Requires AC Power)</p>	<p>Ring Indicator Light located on the phone panel for visual ring indication</p>	

PROVIDING EXCELLENT PRODUCT & SERVICE YOU CAN TRUST, SINCE 1930