

LARGE STAINLESS STEEL SPEAKERPHONE PANEL

560 & 561 STAINLESS STEEL FLUSH OR WALL MOUNT SPEAKERPHONE PANELS

The CEECO Model SSP-561 vandal resistant, stainless steel, handsfree speakerphones offer clear, reliable communication suitable for courtesy, emergency, and entrance security for locations such as hospitals, colleges, airports, and buildings. These large panel speakerphones come equipped with press to start, press to stop call button for the initiation and termination of phone call operation and an LED visual call process indication light. Also available are features such as Call restrictions, ADA, and speed dial. These panels include the flush rough-in mounting box and can be flush mounted into a customer's designed mounting or can be mounted on the wall with our optional attractive surface mounting box (-SW).



Made in the USA

Features

Vandal Resistant, Stainless Steel Construction with Security Hardware

Flush Mount with Rough-In Mounting Box Included

Phone can not be left off-hook. Phone will reset itself when called party disconnects

Programmable Call Restrictions

Flush rough-in mounting box Included or Optional attractive Wall Mounting Box (-SW)


Requires 301-064 Security Tool for Installation

Line Powered

1 Year Warranty and Lifetime Support

SPECIFICATIONS

Panel Size:	10.12"W x 13.12"H 2"D (Behind Panel) 2.65"D (With Wall Mounting Box)
Weight:	Approximately 6 lbs.
Mounting Instructions:	Rough-in flush mounting box (Standard) Dimensions: 8.50" W x 11.50"H x 2.75" D 3 mounting holes per side of panel spaced 5.25" apart vertically and two holes spaced 7.8" apart horizontally Surface Wall Mounting Box (-SW) 4 holes spaced 6W" x 9H"
Environment:	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensating
Loop Current:	30mA min to 80mA max
Impedance:	600 ohms
Type Jack:	RJ11C
Ringer Equivalency:	0.4A
UL & FCC Registration:	Certified



CEECO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEECO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. We offer support for the life of the product! CEECO is devoted to giving you the quality and service you deserve.

LARGE STAINLESS STEEL SPEAKERPHONE PANEL

560 & 561 STAINLESS STEEL SPEAKERPHONE PANELS

KEYPAD SPEAKERPHONE PANELS		AUTO DIAL SPEAKERPHONE PANELS		RING-DOWN SPEAKERPHONE PANELS	
SSP-561-F	SPP-561-FD	SSP-561-D or SSP-561-D2	SSP-561-D-SW	SPP-561-X-ADA	SSP-561-X-ADA-SW
Dimensions: 10 1/4"W x 13 1/8"H		Dimensions: 10 1/4"W x 13 1/8"H		Dimensions: 10 1/4"W x 13 1/8"H	
Stainless Steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Rough in Flush mount box or optional surface mount box Vandal Resistant Instruction Window SSP-561-F Model Chrome Dial Keypad (F) <ul style="list-style-type: none"> Ability to allow or block incoming calls Call restriction capability Programmable conversation time-out Optional speed dialing Programmable PBX prefix dialing or access number SSP-561-FD Model Chrome Tone Dial Keypad (F) and Auto Dial Push Button (D) <ul style="list-style-type: none"> Ability to allow or block incoming calls Call restriction capability Programmable conversation time-out Optional speed dialing Programmable PBX prefix dialing or access number 		Stainless Steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Rough in Flush mount box or optional surface mount box SSP-561-D Model Auto Dial Push Button (D) <ul style="list-style-type: none"> Ability to allow or block incoming calls Programmable conversation time-out capability Programmable PBX prefix dialing or access number SSP-561-D2 Model Auto Dial Push Button (D2) <ul style="list-style-type: none"> Will dial a second number if called party doesn't answer first number dialed 		Stainless Steel Speakerphone Panel Puncture and Weatherproof Speaker Press to Start/ Press to Stop Button Rough in Flush mount box or optional surface mount box SSP-561-X Model Ring-down Operation (X) <ul style="list-style-type: none"> Ability to allow or block incoming calls Initiate a call when programmed through a PBX or phone system 	
LOW POWER MODELS					
SSP-560-F, SSP-560-D, SSP-560-X <ul style="list-style-type: none"> Full Function ADA features are NOT available 					

ADDITIONAL OPTIONS **IP - Voice over Internet Protocol Version available on all models (SIP)**

-ADA	-SW	-RIL	Standard rough in mounting box	Additional Options & Features
				Auto Answer (AA) Remote Programming (RP) Voice Announcement (VA)
<ul style="list-style-type: none"> Red/ green LED call progress indicator light Braille Emergency Plate "EMERG. PHONE" Red Push Button 	Stainless steel wall/surface mounting box	Ring Indicator Light located on the phone panel for visual ring indication.	Rough-in flush mounting box Dimensions: 8.50" W x 11.50"H x 2.75" D	