

519 S.W. Park Street  
Okeechobee, FL 34972  
sales@ceeco.net  
www.ceeco.net



Toll Free: 1-888-357-0798  
Direct Tel: 1-863-357-0798  
Facsimile: 1-863-357-0006

# WPP WEATHERPROOF TELEPHONES

## 331 & 333 WPP WEATHERPROOF TELEPHONES

*Weatherproof cast aluminum housing with stainless steel panel*

The CEECO WPP 331 Series, Vandal Resistant, Weatherproof Telephone enclosed in a rugged cast aluminum housing with an 18" armored cord handset, is built to withstand adverse weather conditions, as well as indoor environments that need that added protection. Installed inside the housing is a high grade stainless steel panel to eliminate rust and corrosion and to provide an attractive finish. The telephone is equipped with tamper resistant hardware to protect it from vandalism and theft as well as over-voltage protection to help guard against surging that might be generated by various conditions and weather.



Made in the USA

### FEATURES

#### Measurements:

12 5/8" H x 9 1/2" W x 8" D (including door)

Stainless Steel Construction with Tamper Resistant Hardware

Designed for Rugged Indoor and Outdoor Environments

Weatherproof Cast Aluminum Housing in Black, Red, Yellow, or Gray

High Quality Stainless Steel Panel Telephone


Armored Cord, Hearing Aid Compatible, Industrial Strength Handset

Marine Quality, Chrome Plated Hookswitch and Tone Dial Keypad

Replacement & Repair Parts Available for Purchase

301-064 Security Tool ( Required for Installation)

One Year Warranty and Lifetime Support



*CEEEO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEEEO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. We offer support for the life of the product! CEEEO is devoted to giving you the quality and service you deserve.*

**PROVIDING EXCELLENT PRODUCT & SERVICE YOU CAN TRUST, SINCE 1930**










# WPP WEATHERPROOF TELEPHONES

## 331 & 333 WPP WEATHERPROOF TELEPHONES

KEYPAD WEATHERPROOF PHONES		AUTO DIAL WEATHERPROOF PHONES		OTHER WEATHERPROOF PHONES	
WPP-331-F-CCH5-Y	WPP-333-FD	WPP-333-DD-Y	WPP-331-D-BR-R	WPP-333-E-G	WPP-331-X-IVC-ST
					
<b>Dimensions:</b> 12 5/8" H x 9 1/2" W x 8" D		<b>Dimensions:</b> 12 5/8" H x 9 1/2" W x 8" D		<b>Dimensions:</b> 12 5/8" H x 9 1/2" W x 8" D	
<p>Weatherproof Cast Aluminum Housing with Stainless Steel Panel Chrome Hookswitch and Cradle 18" Armored Cord Handset</p> <ul style="list-style-type: none"> <li>Hearing aid compatible</li> </ul> <p><b>WPP-331-F Model</b> <b>Chrome Tone Dial Keypad (F)</b></p> <ul style="list-style-type: none"> <li>Ability to allow incoming or outgoing calls</li> </ul> <p><b>WPP-333-F Model</b> <b>Chrome Tone Keypad (F)</b> <b>SMART Features</b></p> <ul style="list-style-type: none"> <li>Ability to allow or block incoming calls</li> <li>Call restriction capability</li> <li>Option to auto dial PBX or access numbers</li> <li>Programmable conversation time-out</li> <li>Optional speed dialing</li> </ul> <p><b>WPP-333-FD Model</b> <b>Chrome Tone Dial Keypad (F) SMART Features and a Auto Dial Push Button (D)</b></p> <ul style="list-style-type: none"> <li>Can be programmed to dial up to 25 digits</li> <li>Optional access code prefix dialing</li> </ul>		<p>Weatherproof Cast Aluminum Housing with Stainless Steel Panel 18" Armored Cord Handset</p> <ul style="list-style-type: none"> <li>Hearing aid compatible</li> </ul> <p><b>WPP-331-D Model</b> <b>Automatic Tone Dialer (D)</b></p> <ul style="list-style-type: none"> <li>Activated when the handset is lifted</li> <li>Will auto dial a single number from 1-11 digits</li> </ul> <p><b>WPP-333-D Model</b> <b>Automatic Dialer (D) SMART Features</b></p> <ul style="list-style-type: none"> <li>Activated when the handset is lifted</li> <li>Can be programmed to dial up to 25 digits</li> <li>Optional access code prefix dialing</li> <li>Ability to allow or block incoming calls</li> </ul> <p><b>WPP-333-DD Model</b> <b>Two Auto Dial Push Button (DD)</b></p> <ul style="list-style-type: none"> <li>Three programmable auto dial buttons</li> <li>Ability to allow or block incoming calls</li> </ul>		<p>Weatherproof Cast Aluminum Housing with Stainless Steel Panel Chrome Hookswitch and Cradle 18" Armored Cord Handset</p> <ul style="list-style-type: none"> <li>Hearing aid compatible</li> </ul> <p><b>WPP-331-X</b> <b>Ring-down Operation (X)</b></p> <ul style="list-style-type: none"> <li>Activated when the handset is lifted</li> <li>Ability to allow incoming calls</li> <li>Initiate a call when programmed through a PBX or phone system</li> </ul> <p><b>WPP-333-E-M Model</b> <b>12 Button Auto Dial Keypad (E)</b></p> <ul style="list-style-type: none"> <li>Each button is programmable to speed dial a single number from 1-23 digits</li> <li>Label area provided to list call destination next to each button</li> <li>Ability to allow or block incoming calls</li> <li>Speed dial capability only, no other calls allowed</li> </ul>	

### ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-M	-IVC	-CCH5	-LB	Weatherproof Housing	-ST/-SB/-RST	-RIL	-SP	Pole Mount
								
Sealed Magnetic Hookswitch	Push Button Volume Control	5 foot Industrial Strength Coiled Cord	Handset w/ internal steel lanyard (braided metal rope) and lanyard mounting bracket that is secured onto panel for added strength.	Standard Black & TELEPHONE on Door <b>-B-EMER</b> Black & EMERGENCY on Door <b>-R</b> Red & EMERGENCY on Door <b>-R-TEL</b> Red & TELEPHONE on Door <b>-Y</b> Yellow & EMERGENCY on Door <b>-Y-TEL</b> Yellow & Telephone on Door <b>-G</b> Grey & TELEPHONE on Door <b>-G-EMER</b> Grey & EMERGENCY on Door	Blue Strobe Light option:	Ring Indicator Light located on the phone panel for visual ring indication.	Spring loaded door option	Pole Mounting bracket fits poles 2.5" - 6".
<ul style="list-style-type: none"> <li>Completely Sealed</li> <li>No Moving Parts</li> </ul>	<ul style="list-style-type: none"> <li>Background Noise reduction</li> </ul>				<ul style="list-style-type: none"> <li>Steady on</li> <li>Flashing</li> <li>For location visibility</li> <li>Requires AC power</li> </ul>			