



BOSTIK 3206E

SOLVENT BASED ADHESIVE

KEY FEATURES

- Cleanliness of use
- Produces tough bonds
- Excellent adhesion to both plasticised and un-plasticised PVC

DESCRIPTION

Bostik 3206E is a solvent-borne, polyurethane based adhesive for general purpose use.

RECOMMENDED USE

Bostik 3206E is suitable for many industrial applications and will bond a wide variety of surfaces including wood, canvas, leather, PVC, nylon fabric, polyurethane coated fabric, polyurethane rubber, PVC and polyurethane foam, polycarbonate, ABS and decorative laminated plastics.

NOTE: To obtain enhanced properties with better resistance to high temperatures and fluids **Bostik 3206E** may be used in conjunction with **Bostikure D** as a two part, cold curing adhesive system

IMPORTANT

Before embarking on any work involving **Bostik 3206E** the safety data sheet should be carefully studied by those carrying out the work.

BSI STANDARDS



METHOD OF USE

SURFACE PREPARATION

- Thoroughly clean and dry both surfaces, abrading where applicable.

ADHESIVE PREPARATION

When using as a two part system with **Bostikure D** the mix ratio is 100 parts of adhesive to 6 parts of **Bostikure D** (by weight) or by taking:

Bostik 3206E	Bostikure D
1 litre tin	D40 bottle
5 litre tin	D200 bottle

The pot life of the mixed adhesive in a closed container is approximately 8 hours at normal room temperatures.

APPLICATION & BONDING

- Apply an even film of adhesive to both surfaces with a brush or serrated trowel. The latter is ideal for covering large areas, if spray application is preferred the adhesive should be diluted with an equal volume of **Cleaner 1**
- Allow the two films to dry for approximately 5 to 10 minutes. This range should be checked if possible with the particular material to be bonded. With thin adhesive films, which are created by very absorbent surfaces or merely brushing out thinly, it is advisable to allow the first coat to dry for at least 20 minutes, apply a second coat and leave 5 to 15 minutes before bonding.
- Bring the two coated surfaces together using sufficient pressure to ensure intimate contact.

NOTE: Polyurethane adhesives of the **Bostik 3206E** type do not have the same aggressive tack property as that of polychloroprene contact adhesives. Bond open times are accordingly shorter and greater pressures are required when the bonds are made.

N.B. In certain cases it may be possible to use other bonding techniques such as one way wet or semi-wet stick, heat or solvent activation. In all cases, however, preliminary tests must be carried out to determine suitability.

TYPICAL CHARACTERISTICS

Physical form	Semi viscous liquid
Colour	Clear, slightly amber
Chemical type	Polyurethane/resin based solution
Odour	Predominantly ketone
Solvent	Mixture of ketones & toluene
Flammability	Highly flammable
Flash Point (closed cup)	In the group - 18 to -7°C
Viscosity, Brookfield RVT, 20rpm at 25°C	[mPa.s] Approx. 3000
Total solids content	[%] Approx. 22
Relative density	Approx. 0.9
Coverage	Approximately 4m ² per litre (2m ² per litre bonded area)
Temperature resistance	-20 to +80°C (-20 to +100°C when cured with Bostikure D)
Water resistance	Good

Oil, petrol & kerosene resistance	Good
Staining	Generally non-staining but on light coloured, thin PVC very slight staining may occur under extreme conditions. NB Exposed adhesive film turns brown.
Cleaner	Use Cleaner 1 for surface cleaning, the removal of surplus adhesive and for cleaning application equipment

Disclaimer – please read carefully

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products..

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, or its liability for fraud, or fraudulent misrepresentation, or any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including

PACKAGING

Please refer to Customer Service Department for current pack sizes.

STORAGE

Store in a cool well ventilated place in the temperature range 10 – 30°C. Treat as flammable/combustible – Keep away from oxides, heat and flames.

SHELF LIFE

At least 12 months from date of manufacture, closed in original packaging under the above conditions of storage.

in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number on the bottom right hand side of this page.

SMART HELP

Please contact your local representative

