

Anixter Level 3 for Industrial Network Environments

Industrial Ethernet Cable: Cat 5e 24-4 Pair Solid UTP



L3-5E-SOL-UTP-02	4 PR 24 AWG solid bare copper conductors, polyolefin insulation, rip cord, PVC inner jacket, 0.035" wall industrial grade sunlight- and oil-resistant PVC outer jacket. EtherNet/IP™
-------------------------	--

Physical Characteristics (Overall)	
Conductor	
# Pairs	4
AWG	24
Stranding	Solid
Material	BC - Bare Copper
Diameter	.02 in.
Total # of Conductors	8
Insulation	
Material	PO - Polyolefin
Wall Thickness	.009 in.
Diameter	.035 in.
Stranding	7x32
Conductor Material	TC – Tinned Copper
Inner Jacket	
Material	PVC - Polyvinyl Chloride
Nominal Diameter	.2 in.

Outer Jacket	
Material	Industrial Grade PVC - Polyvinyl Chloride
Nominal Wall Thickness	.035 in.
Outer Jacket Ripcord	Yes
Overall Cable	
Overall Nominal Diameter	.285 in.
Pair Color Code Chart	
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown
Mechanical Characteristics (Overall)	
Installation Temperature Range	-25°C To +75°C
Operating Temperature Range	-40°C To +75°C
Max. Recommended Pulling Tension	40 lbs.
Applicable Specifications and Agency Compliance (Overall)	
Applicable Standards & Environmental Programs	
CEC/C(UL) Specification	CMR
NEC/(UL) Specification	CMR, CMX-Outdoor
EU Directive 2011/65/EU (ROHS II)	Yes
Other Standards	ISO/IEC 11801 ed 2.1 (2008) Class D
EU Directive 2000/53/EC (ELV)	Yes
EU Directive 2002/95/EC (RoHS)	Yes
EU RoHS Compliance Date (mm/dd/yyyy)	01/01/2004
EU Directive 2002/96/EC (WEEE)	Yes
EU Directive 2003/11/EC (BFR)	Yes
CA Prop 65 (CJ for Wire & Cable)	Yes
MII Order #39 (China RoHS)	Yes
Telecommunication Standards	Category 5e - TIA 568.C.2

Other Specification	NEMA WC-63.1 Category 5e, Ethernet/IP™ compliant, UL verified to Category 5e
Flame Test	
UL Flame Test	UL1666 Vertical Riser
CSA Flame Test	FT4
Suitability	
Suitability - Indoor	Yes
Suitability - Outdoor	Yes
Sunlight Resistance	Yes
Oil Resistance	Yes
Plenum/Non-Plenum	
Plenum (Y/N)	No

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
 Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.