

Anixter Level 2 for Industrial Network Environments

Industrial Ethernet Cable: Cat 5e 24-4 Pair Solid UTP



L2-5E-SOL-UTP-02	4 Pair 24 AWG UTP solid bare copper conductors, polyolefin insulation, industrial grade sunlight- and oil-resistant PVC jacket, rip cord. EtherNet/IP™
-------------------------	--

Physical Characteristics (Overall)	
Conductor	
# Pairs	4
AWG	24
Stranding	Solid
Material	BC - Bare Copper
Diameter	0.02 in.
Total # of Conductors	8
Insulation	
Material	PO - Polyolefin
Wall Thickness	0.009 in.
Diameter	0.035 in.
Outer Shield	
Type	Unshielded
Outer Jacket	
Material	Industrial Grade PVC - Polyvinyl Chloride
Outer Jacket Ripcord	Yes

Overall Cable	
Overall Nominal Diameter	0.23 in.
Pair Color Code Chart	
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown
Mechanical Characteristics (Overall)	
Installation Temperature Range	-25°C To +75°C
Operating Temperature Range	-40°C To +75°C
Bulk Cable Weight	82 lbs.
Max. Recommended Pulling Tension	40 lbs.
Min. Bend Radius/Minor Axis	2.5 in.
Applicable Specifications and Agency Compliance (Overall)	
Applicable Standards & Environmental Programs	
CEC/C(UL) Specification	CMR
NEC/(UL) Specification	CMR, CMX-Outdoor, UL444
EU Directive 2011/65/EU (ROHS II)	Yes
EU Directive 2000/53/EC (ELV)	Yes
EU Directive 2002/95/EC (RoHS)	Yes
EU RoHS Compliance Date (mm/dd/yyyy)	1/1/2004
EU Directive 2002/96/EC (WEEE)	Yes
EU Directive 2003/11/EC (BFR)	Yes
CA Prop 65 (CJ for Wire & Cable)	Yes
MII Order #39 (China RoHS)	Yes
Other Specification	NEMA WC-63.1 Category 5e, UL verified to Category 5e
PMSHA Specification	P-07-KA060003
Flame Test	
UL Flame Test	UL1666 Riser
CSA Flame Test	FT4
IEEE Flame Test	1202

Suitability	
Suitability - Outdoor	Yes
Sunlight Resistance	Yes
Oil Resistance	Yes
Plenum/Non-Plenum	
Plenum (Y/N)	No

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations

to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW,
ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED,
ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.