

# Model #: SRW9U

## SmartRack 9U Wall Mount Rack Enclosure Cabinet



#### **Highlights**

- Designed for IT and education environments where equipment needs to be secure and out of the way
- 9U with adjustable front vertical rackmount rails
- . Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance

### **Description**

The SRW9U 9U Wall Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 9U of standard 19" rackmount equipment. Supports up to 140 lbs of equipment. A sturdy wall-mount bracket allows the cabinet to quickly be hung on the wall.

#### Applications

IT network environments with limited floor space and classrooms where equipment needs to be secure and out of the way of students.

#### **Features**

- 9U wall-mounted enclosure
- Adjustable mounting depths up to 17" inches
- Ventilated front door and side panels for increased airflow
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance
- 5 year warranty

### **Specifications**

PHYSICAL	
Installed whole system maximum rack depth (inches)	16.5
Installed whole system minimum rack depth (inches)	3
Installed whole system total rack space height (rack spaces)	9U

Shipping weight (lbs)	38.4
Shipping weight (kg)	17.41
Shipping Dimensions (HWD/in)	22.6 x 26.4 x 20.5
Unit weight (Ibs)	35
Unit weight (kg)	15.875
Unit Dimensions (in)	19.88 x 23.62 x 17.78
Color	Black
Weight Capacity - Stationary (Ibs)	200
SPECIAL FEATURES	
Grounding lug	Front and Back door frames
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	UL60950; RoHS
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	5-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModeIID=4895.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.