

## FS-DM-DOME

### *Bid-Spec*

#### **1.0 Description**

The FS-DM-DOME is a dome housing that has been manufactured to protect the Pro Series 360° cameras against water, dust, and other minor weather hazards with an IP66 rating. Its housing design permits unhindered 360° viewing for indoor or outdoor applications with easy installation. It has been produced with die-cast aluminum materials, powder coating, and a high impact-resistant, ultra-transparent cover that make this housing durable and reliable.

#### **2.0 Bid Specification**

- This accessory shall be compatible with the Pro Series 360° cameras.
- This accessory shall be mounted to a wall using the FS-DM-WALL with a FS-DM-POLE or FS-DM-CORNER, or it shall be mounted in the ceiling using the FS-DM-CEILING.
- This accessory shall feature an aluminum housing that is IP66 rated.
- This accessory shall be used for indoor and outdoor applications.
- This accessory shall be compatible with IEEE802.3af PD.
- This accessory shall be supplied with one 5mm Wrench, four Plastic Expansion Plugs, four M4 Steel Screws, and one Network Cable.
- This accessory shall contain Auto-Restart Fault Management.
- This accessory shall feature In-rush Current Limit, Over-current Protection.
- This accessory shall have an operating temperature of -40° C (-40° F) to 60° C (140° F) with 0-95% humidity.

## FS-DM-DOME

### Quick-Spec

#### 3.0 Minimum Performance Specification

The FS-DM-DOME accessory will meet the following operating requirements:

**Mechanical**

Dimensions	5.75 x 6.5 in (146.05 x 165.1 mm)
Weight	3.97 lbs (1801 g)
Construction	Body- Aluminum (ADC-12) Window- Transparent Cover

**Environmental**

Certificates	IP66
Operating Temperature	-40° C to 60° C (-40° F to 140° F)
Humidity	0-95%

<b>Compatibility</b>	FS-DM-WALL, FS-DM-CEILING
----------------------	---------------------------

**Model Number**

- FS-DM-DOME

**Warranty**

- *Minimum 3 Year Parts and Labor*

**FS-DM-DOME**

*Sentry360, Inc. reserves the right to change products or specifications without notice.*