

BC Personal 120V 350VA 180W Standby UPS, Ultra-Compact Desktop, 6 Outlets

MODEL NUMBER: **BC350**



Highlights

- 350VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

Package Includes

- BC350 UPS System
- Instruction manual

Description

Tripp Lite's BC350 standby UPS offers power protection for PCs, workstations and other sensitive electronics in an attractive space saving, ultra-compact housing. Prevents data loss and system downtime by providing battery-supported AC output during brownouts and blackout conditions. 6 widely spaced output receptacles accommodate large transformer plugs without blocking outlets. 3 outlets with full battery support and surge suppression protect computers, monitors and other vital system components from loss of power; 3 additional surge suppression-only outlets are ideal for printers and other accessories not requiring battery support. Audible alarm and front panel LEDs offer status information regarding line and battery power operation. 350VA/180W power handling ability supports entry-level PCs for up to 12 min. during power failures. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- BC350 standby UPS offers complete protection from blackouts, brownouts and surges
- 6 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 3 battery-supported outlets protect computer, monitor and vital system peripherals; 3 additional surge suppression-only outlets protect printers and other system accessories not requiring battery support
- Space saving right-angle input plug
- Provides battery-derived AC output during blackouts and brownouts
- 350VA/180W power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 12 min. during blackout conditions
- Optional PDUB15 bypass PDU enable hot-swappable UPS replacement with no disruption to connected equipment
- Space-saving, ultra-compact housing fits almost anywhere

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (Watts)	180



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(6) 5-15R
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Half Load Runtime (min.)	10 min. (90w)
DC System Voltage (VDC)	12
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Audible Alarm	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	380
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3 x 10.5 x 5
UPS Power Module Dimensions (hwd, cm)	7.6 x 26.7 x 12.7
UPS Power Module Weight (lbs.)	7.7
UPS Power Module Weight (kg)	3.5
UPS Shipping Dimensions (hwd / in.)	4.5 x 12.5 x 7.8
UPS Shipping Dimensions (hwd / cm)	11.4 x 31.8 x 19.7
Shipping Weight (lbs.)	10
Shipping Weight (kg)	4.5
UPS Housing Material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	39.1
Battery Mode BTU / Hr. (Full Load)	53.2
AC Mode Efficiency Rating (100% Load)	94%
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	139
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.