



DATE: 3-13-15

PRODUCT SPECIFICATION 13878 O

TYPE: TelcoFlex® III / KS24194™ L3
 Central Office Power Wire and Cable
 Low Smoke, Non-Halogenated Insulated (With Cotton Braid)
 Lead-Free and Silicone Free, Meets European RoHS Directive
 105°C Dry, 60°C Wet - 600 Volts
 UL Listed RHH/ST1 and VW-1
 UL Listed "For CT Use" (1/0 & Larger)
 CSA AWM I B 105°C, 600 V. FT4
 Audited by Telcordia to all 33 requirements of GR-347-CORE
 Meets all requirements of ATIS-0600017.2014
 Meets IEC including 60674 & 60332
 REACH – European Community Regulation

SIZE: 14 AWG thru 750 KCMIL - Single Conductor

I. SCOPE:

This specification covers the construction requirements for low smoke, non-halogenated central office power wire and cable, insulated with Southwire TelcoHyde® 5221. UL listed Type RHH/ST1 with cotton braid for use in accordance with the National Electrical Code. The construction of the wire and cable is in accordance with Telcordia GR-347-CORE, Underwriters' Laboratories requirements, and the requirements of CSA for the FT4 flame/smoke test. Sizes 1/0 AWG and larger are UL "CT Use" (Cable Tray) rated.

II. CONSTRUCTION:

SIZE (AWG or KCMIL)	STRANDING	NOMINAL CMA	NOMINAL CONDUCTOR DIAMETER (INCHES)	INSUL. MIN. AVG. WALL (MILS)	NOMINAL INSUL. DIAM. (INCHES)	NOMINAL BRAID DIAM. (INCHES)	MAX D.C. RES. @ 20°C (OHMS/M')	AMPACITY PER NEC TABLE 310.15(B)(16)	
								75°C	90°C
14	7/.0247"	4110	.0708	45	.164	.226	2.730	20	25
12	7/.0311"	6530	.0892		.182	.244	1.720	25	30
10	7/.0392"	10380	.1130		.210	.272	1.080	35	40
8	7/.0495"	16510	.1420	60	.265	.327	0.6795	50	55
6	7/.0624"	26240	.1780		.304	.370	0.4276	65	75
4	7/.0787"	41740	.2250		.348	.414	0.2689	85	95
2	7/.0992"	66360	.2830		.406	.482	0.1691	115	130

Continued



II. CONSTRUCTION (Continued):

SIZE (AWG or KCMIL)	STRANDING	NOMINAL CMA	NOMINAL CONDUCTOR DIAMETER (INCHES)	INSUL. MIN. AVG. WALL (MILS)	NOMINAL INSUL. DIAM. (INCHES)	NOMINAL BRAID DIAM. (INCHES)	MAX D.C. RES. @ 20°C (OHMS/M')	AMPACITY PER NEC TABLE 310.15(B)(16)	
								75°C	90°C
1/0	19/.0760"	105600	.3620	80	.530	.606	0.1063	150	170
2/0	19/.0853"	133100	.4050		.579	.651	0.08432	175	195
4/0	19/.1076"	211600	.5120		.688	.756	0.05248	230	260
350	37/.0991"	350000	.6610	95	.854	.930	0.03206	310	350
500	37/.1185"	500000	.7900		.983	1.059	0.02222	380	430
750	61/.1130"	750000	.9680	110	1.200	1.276	0.01481	475	535

A. CONDUCTORS:

Class B stranded, tin-coated copper conforming to ASTM B-33 and Underwriters' Laboratories requirements. An opaque Mylar tape shall be applied over the conductor to facilitate stripping.

B. INSULATION:

105°C rated low smoke, non-halogen TelcoHyde® 5221 conforming to Underwriters' Laboratories Standard 44, Subjects 509 and 758, and CSA C22.2 No. 210-11. In addition, TelcoHyde® 5221 complies with the requirements of Telcordia Specification GR-347-CORE. The insulation has a Limiting Oxygen Index of 35%.

C. SEPARATOR:

On sizes 6 AWG and larger, a 1 mil clear Mylar tape shall be applied over the insulation.

D. COVERING:

On all sizes, a natural cotton braid conforming to UL Standard 44 requirements is applied overall. A section of completed cable has a Limiting Oxygen Index of 35%.

E. FINISH:

A moisture resistant, fire retardant saturant and a colored finisher are applied to the braid.



Southwire[®]

AIW[™]
CORD BRAND

PS-13878 O
DATE: 3-13-15

F. SURFACE MARKING:

Two sides of the cable shall be printed using an ink of a contrasting color and with the following information:

“SOUTHWIRE AIW[™] CORD BRAND TELCOFLEX[®] III/KS24194[™] L3 NON-HAL (UL) E18321 SIZE (AWG or KCMIL) 600 VOLTS RHH ST1 FT4 OR AWM 3578 60°C WET VW-1 --- LL8825 CSA AWM I B 105°C 600 VOLTS FT4 YEAR TIME JULIAN DATE --- MEETS IEC INCLUDING 60674 & 60332”

Add “FOR CT USE” before “(AWM3578)” on Sizes 1/0 AWG and larger. Sequential footage markings shall be applied at 2 foot intervals on one side of the cable.

G. TESTING:

Physical and electrical tests in accordance with the requirements of UL Standard 44, Subject 509 and 758, and CSA Standard C22.2 No. 210-11 as AWM.

H. LABELS:

UL and CSA tags and labels shall be applied to all packages.

I. LENGTHS:

All put-ups one length only unless agreed to otherwise. Maximum lengths per size will be advised.

J. PACKAGING:

The ends of the cable shall be capped or taped to prevent the entrance of moisture during shipment or storage.



Southwire®



PS-13878 O
DATE: 3-13-15

K. PART NUMBERS for TelcoFlex® III / KS24194™ L3:

SIZE	COLOR							
	GRAY	GREEN	BLUE	RED	BLACK	RED -	BLUE -	GRAY
						BLACK TRACER	BLACK TRACER	BLACK TRACER
750	56961301	56961501	56961101	56961701	58203701	57126201	56961201	56961401
500	56963301	56963501	56963001	57155501	56962901	56963601	56963101	56963401
350	56980801	57156901	57149201	56981001	57138201	56981101	56980701	56980901
4/0	56984501	56984701	56984301	56984901	56984201	56985001	56984401	56984601
2/0	56977701	56977901	56977501	56978101	57138301	56978201	56977601	56977801
1/0	56966701	56966901	56966401	56967001	57138401	56967101	56966601	56966801
2	56975701	56976001	56976101	56975801	56975901	56976201	56976301	56976501
4	56982601	56982801	56982401	56982901	57128701	56983101	56982501	56982701
6	56986401	56986501	56986201	56986601	56986101	56986701	57149101	57141001
8	57126701	56988001	57149001	56988101	56987901	W39811	W39812	W40771
10	57051101	56968201	56968001	56968301	56967901	56968401	W39806	
12	56969501	56969601	56969401	56969701	56969301	W39799	W39800	
14	57133601	57145701	57155601	57133701	57133501	W39793	W39794	

