


STAINLESS STEEL TELEPHONE PANELS

311, 313 STAINLESS STEEL KEYPAD TELEPHONE PANELS

Flush Mount or Replacement Panel for Weatherproof (WPP) or Open Enclosure Housings (HOB)

Discover **CEE CO's** SSP 311 series keypad telephones which are our most universal model, because these panels can be everything you need for both indoor and outdoor use. These sturdy, yet premium telephones can be flush mounted or be installed in our durable, yet attractive weatherproof (WPP) or open enclosure housings (HOB). These stainless steel panels are proven to fit all your security, emergency, and courtesy telephone needs at a wide range of locations including hospitals, schools universities, prisons, airports, pools, golf courses, office builds and more. CEE CO's dedicated sales team, knowledgeable technical support, and readily available telephones and parts gives you the product and service you can count on. Manufactured in the USA, CEE CO telephones are Built to Last and are supported by over 84 years of experience.



FEATURES

Measurements:

7 1/6"W x 11 1/4"H x 4 1/4"D (with handset on hook)

Weight 5 lbs

Stainless Steel Construction with Tamper Resistant Hardware

Marine Quality Chrome Hookswitch

Vandal Resistant Chrome Tone Dial

Hearing Aide Compatible Armored Cord Handset


Can be Installed in an Open Enclosure (HOB) or a Weatherproof Housing (WPP)

Line Powered

Requires 301-064 Security Tool for Installation

1 Year Warranty and Lifetime Support

PANEL HOUSINGS















PANEL SPECS

CEE CO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEE CO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. We offer support for the life of the product! CEE CO is devoted to giving you the quality and service you deserve.

PROVIDING EXCELLENT PRODUCT & SERVICE YOU CAN TRUST, SINCE 1930

311/313 STAINLESS STEEL TELEPHONE PANELS

KEYPAD PANEL PHONES		AUTODIAL PANEL PHONES		OTHER PANEL PHONES	
SSP-311-F or SSP-313-F	SSP-313-FD	SSP-311-D or SSP-313-D	SSP-313-DD	SSP-311-X-M-IVC	SSP-313-E
					
Dimension: 7 1/6"W x 11 1/4"H x 4 1/4"D		Dimension: 7 1/6"W x 11 1/4"H x 4 1/4"D		Dimension: 7 1/6"W x 11 1/4"H x 4 1/4"D	
Stainless Steel, Telephone Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset <ul style="list-style-type: none"> Hearing aid compatible Optional cord lengths SSP-311-F Model Chrome Tone Dial Keypad (F) <ul style="list-style-type: none"> Will allow incoming or outgoing calls SSP-313-F Model Chrome Tone Dial Keypad (F) SMART Features <ul style="list-style-type: none"> Will allow or block incoming calls Call restriction capability Option to auto dial PBX or access numbers Programmable conversation time-out Optional speed dialing SSP-313-FD Model Chrome Tone Dial Keypad (F) SMART Features and a Auto Dial Push Button (D) <ul style="list-style-type: none"> Can be programmed to dial up to 25 digits Optional access code prefix dialing 		Stainless Steel, Telephone Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset <ul style="list-style-type: none"> Hearing aid compatible Optional cord lengths SSP-311-D Model Automatic Dialer (D) <ul style="list-style-type: none"> Activated when the handset is lifted Will allow incoming calls Will auto dial a single number from 1-11 digits SSP-313-D Model Automatic Dialer (D) SMART Features <ul style="list-style-type: none"> Can be programmed to dial up to 25 digits Optional access code prefix dialing No incoming calls allowed SSP-313-DD Model Auto Dial Push Button (DD) <ul style="list-style-type: none"> Two programmable auto dial buttons that will auto dial a single number from 1-11 digits Ability to allow or block incoming calls 		Stainless Steel, Telephone Panel Chrome Hookswitch and Cradle 32" Armored Cord Handset <ul style="list-style-type: none"> Hearing aid compatible Optional cord lengths SSP-311-X Model Ring-down Operation (X) <ul style="list-style-type: none"> Activated when the handset is lifted Will allow incoming calls Initiate a call when programmed through a PBX or phone system SSP-313-E Model 12 Button Auto Dial Keypad (E) <ul style="list-style-type: none"> Each button is programmable to speed dial a single number from 1-23 digits Label area provided to list call destination next to each button Ability to allow or block incoming calls Speed dial capability only, no other calls allowed 	

ADDITIONAL OPTIONS									IP - Voice over Internet Protocol Version available on all models (SIP)	
-M	-IVC	-ACH**	-ACH*	-CCH*	-LB	Open Enclosure Housing	Weatherproof Housing	-RIL		
										
Sealed Magnetic Hookswitch <ul style="list-style-type: none"> Completely Sealed No Moving Parts 	Internal Volume Control <ul style="list-style-type: none"> Push Button Volume Control Background Noise reduction 	Varies armored cord from length 14" to 72" Example: ACH14: 14" armored cord	Varies handset color -ACHW White handset -ACHR Red handset	Coiled cord available from 5', 10', & 15' (feet). Example: -CCH5 5' Long	Handset w/ internal steel lanyard (braided metal rope) and lanyard mounting bracket that is secured onto panel for added strength.	-331-HOB Standard Black Housing -331-HOB-R Red Housing -331-HOB-S Stainless Steel Housing	-331-005 Standard Black & TELEPHONE on Door -331-005-EMER Black & EMERGENCY on Door -331-005-R Red & EMERGENCY on Door -331-005-R-TEL Red & TELEPHONE on Door -331-005-Y Yellow & EMERGENCY on Door -331-005-Y-TEL Yellow & Telephone on Door 331-005-G Grey & TELEPHONE on Door 331-005-G-EMER Grey & EMERGENCY on Door	Ring Indicator Light located on the phone panel for visual ring indication		