

MHD-341-F-IVC SPECIFICATIONS

MAGNETIC HOOKSWITCH DESK TELEPHONE WITH KEYPAD


Standard Analog Power, but also available in VoIP versions

Completely sealed dust and corrosion protected desktop stainless steel telephone with impenetrable magnetic hookswitch incased in housing. Operates as a standard dialing telephone. Equipped with a marine quality chrome metal tone dial keypad, 32" hearing aid compatible magnetic handset, internal volume control via volume control button with loudness symbol and background noise minimization, and steel mounting backplate.



SPECIFICATIONS

Panel Size:	6.37" W x 9.75" H x 4" D
Weight:	Approximately 7 lbs.
Mounting Instructions:	Separate the cover assembly from the backplate assembly by pulling the bottom forward and lifting up. The backplate assembly is designed rest on any flat surface.
Environment:	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensating
Input Power:	Telephone Line Powered
Loop Current:	23mA min to 80mA max
Impedance:	600 ohms
Type Jack:	RJ11C
Ringer Equivalency:	0.4A
Hearing Aid Compatible:	Meets EIA standards
UL& FCC Registration:	Certified
ACCESSORIES:	301-037 Security Tool (required for installation)



ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-IVC	-BR	-ACH18	-CCH5	-RIL	#301-037
Push Button Volume Control • Background Noise reducer	Braille "EMER PHONE" plate on panel	18" Armored Cord Handset	5 foot Industrial Strength Coiled Cord	Ring Indicator Light located on the phone panel for visual ring indication	Security Tool (Required for installation)



Providing Telecommunication Solutions Since 1930

Communication Equipment
& Engineering Company

<http://www.ceeco.net>

Email: sales@ceeco.net

519 SW Park Street

Okeechobee, FL

Voice 863-357-0798

Fax 863-357-0006