

## T250I0X2



Article Number: 111-00507

Heavy Duty Cable Tie, 28.7" Long, 250 lb Tensile Strength, PA66, Black, 25/pkg



Download spec sheet

### Base Data

Local Order Number T250I0X2

Type T250I

Color Black (BK)

**Features and Benefits**

- Heavy duty design to offer higher tensile strength.
- Buckle feature on head allows excess strap to be tucked away after installation.

**Product Description** HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Variant Inside Serrated

Short Description Heavy Duty Cable Tie, 28.7" Long, 250 lb Tensile Strength, PA66, Black, 25/pkg

### Product Dimensions

Minimum Tensile Strength (Imperial) 250.0 lbs

Minimum Tensile Strength (Metric) 1115.0 N

Length L (Imperial) 28.7 "

Length L (Metric) 730.0 mm

Width W (Imperial) 0.49 "

Width W (Metric) 12.5 mm

Bundle Diameter Min. (Imperial) 0.47 "

Bundle Diameter Min. (Metric) 12.0 mm

Bundle Diameter Max. (Imperial) 8.0 "

Bundle Diameter Max. (Metric) 203.0 mm

### Logistics and Packaging

Package Quantity (Metric) 25

Carton Quantity 500

### Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

CSA Certified No

**Flammability** UL94 V2

**Halogenfree** Yes

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

**ROHS compliant (Article 4 - 1)** Yes

**Certification/Specification** UL ZODZ2.E64139

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** Yes