


ValueLine
Performance and Value



The ComNet™ CNFE1EOC-M modems support Ethernet over twisted pair or coaxial cable, at data rates of up to 90 Mbps. Ethernet data may be transmitted over a telephone-grade twisted copper pair, legacy serial cabling, or standard 75 ohm coaxial cable circuits, making this unit ideal for those applications where it is desired to utilize an existing installed base of copper wiring for Ethernet transmission. These modems are the perfect solution for upgrading a legacy twisted copper or coaxial cable plant for use with Ethernet, when compared to the significant costs of installing new network cabling. The fastest usable data rate is automatically selected, depending upon the transmission distance and cable quality. LED status indicators are provided for rapidly ascertaining the operating status of the modem and the link.

FEATURES

- › A ComNet ValueLine Product - Lower price: designed for installation in benign (0 to +60° C) operating environments.
- › Utilizes latest VDSL2 technology for fastest data rate transmission and greatest transmission distance
- › Ideal for multiple-channel Ethernet over VDSL applications where modem space may be limited
- › Supports transmission distances of up to 10,000 ft (3 km) over twisted copper, or up to 1500 ft (457 m) over coaxial cable
- › Symmetric line rates of over 91 Mbps
- › Automatically sets fastest possible data rate vs. cable quality and transmission distance
- › User-configurable master/remote, forward error correction, asymmetrical/symmetrical data, and long-reach/short-reach selection
- › IEEE 802.3 Compliant. 10/100 BASE-T/TX Ethernet port with automatic MDI/MDI-X crossover
- › Screw Terminals for twisted copper circuits, or BNC connector for coaxial cable
- › A smaller-sized package for stand-alone mounting only, for use in those applications where space may be limited
- › Five year warranty

APPLICATIONS

- › Ethernet transmission over existing copper telephone-grade, serial or 75Ω coaxial cable

SPECIFICATIONS

Interface

Ethernet Port	Ethernet connector	RJ45
	Cable	Cat 5, Cat 5e, Cat 6
	Data Rate	10/100Mbps
	Distance	100m (328ft)

Line Side Port 1 (Twisted Pair)

UTP connector	Screw Terminal Block	
Cable	Telephone-grade 19 to 26 AWG (one twisted pair)	
Throughput	(Downstream / Upstream)	
1000 ft (305 m)	70 Mbps / 68 Mbps	
2500 ft (762 m)	26 Mbps / 17 Mbps	
5000 ft (1524 m)	16 Mbps / 1 Mbps	
7500 ft (2286 m)	5 Mbps / 0.5 Mbps	
10,000 ft (3048 m)	1 Mbps / 0.25 Mbps	

Line Side Port 2 (75Ω Coax)

Coaxial connector	BNC	
Impedance	75 ohm coax	
Throughput	(Downstream / Upstream)	
200 ft (61 m)	88 Mbps / 95 Mbps	
500 ft (152 m)	85 Mbps / 93 Mbps	
1000 ft (305 m)	83 Mbps / 89 Mbps	
1500 ft (457 m)	76 Mbps / 83 Mbps	

Faster data rates and greater transmission distances thru coaxial cable are possible, depending upon the type and quality of the coaxial cable utilized

- User-Configurable Selection of:
- Master/Remote Operation
 - Symmetrical/Asymmetrical Data
 - Forward Error Correction
 - Long or Short Range operation for optimal BER (Bit Error Rate) performance

Power

Operating Voltage Range	12-27 VAC @ or 12-27 VDC
Power Consumption	< 320 mA

Electrical & Mechanical

Overload Protection	Automatic Resettable Solid-State Current Limiters
Circuit Board	Meets IPC Standard
Size (L×W×H)	
Mini	4.1 × 3.7 × 1.1 in (10.4 × 9.4 × 2.8 cm)
Comfit	6.1 × 5.3 × 1.1 in (15.5 × 13.5 × 2.8 cm)
Shipping Weight	<2 lbs./0.9 kg

Environmental


MTBF	>100,000 hours
Operating Temp	0° C to +60° C
Storage Temp	-40° C to +85° C
Relative Humidity	0% to 95% (non-condensing) ¹



ORDERING INFORMATION

Part Number	Description
CNFE1EOC-M	Ethernet over Twisted Pair or Coax, Small Size
CNFE1EOC	Ethernet over Twisted Pair or Coax, ComFit Size
Accessories	24 VAC Power Supply (included)
Options	[1] Add suffix '/C' for Conformally Coated Circuit Boards to extend to condensation conditions (Extra charge, consult factory)

TYPICAL APPLICATION



Low Power Consumption