

Tsunami[®] Multipoint 825 CPE

A High Performance Customer Premises Equipment for WISPs



Presenting Proxim's next generation Point-to-Multipoint Customer Premises Equipment

Proxim Wireless is a leader and an early innovator in wireless technology providing high-speed, long-range broadband wireless solutions. Leveraging the advantages of OFDM, MIMO radio innovations along with Proxim's proprietary Wireless Outdoor Routing Protocol (WORP[®]), Tsunami[®] Multipoint 825 CPE is a feature rich customer premises equipment specifically designed for the carrier, service provider and WISP market.

The low cost outdoor form factor of Tsunami[®] Multipoint 825 CPE is an ideal solution for large-scale wireless deployments suitable for all last-mile broadband wireless access deployments.

This CPE is also feature rich with a carrier-grade prioritization platform supporting multiple service classes that can prioritize voice, video and data applications over the widest range of operating frequencies.

World Class Performance

- Features a very small form factor and an outdoor rated IP67 Metal enclosure
- Available with 15 dBi integrated antenna
- 50Mbps or 100Mbps of throughput with maximum data rates of 300Mbps
- Provides flexible channel planning with support for 5.150 to 5.925 GHz
- Comes with a 2x2 MIMO high power radio capable of 26 dBm transmit power
- Allows flexible bandwidth allocation for service tiers
- Seamless roaming up to 295 km/h (185 mph)

All-in-One CPE with Security & Gateway Features

- Built-in feature rich network protocols for Bridging, Routing and Gateway functionality
- Advanced encryption protects over-the-air transmission via AES-128
- Radio mutual authentication eliminates unauthorized use of the system by rogue subscriber units and man-in-the-middle attacks

- MAC, Ether type, IP address packet filtering provides granular network security
- Uses Proxim's Wireless Outdoor Routing Protocol (WORP[®]) to prevent snooping
- Features highly-secure remote management via SSL, SSH and SNMPv3
- Supports either WORP[®] or WORP[®] sync to adapt to RF condition and deliver optimum performances

Reducing Costs for Wireless ISPs

- License-free frequency bands worldwide provide reliable wireless broadband without the high cost of licensed frequencies
- Low-cost bundle including both radio and mounting kit provides the industry's most aggressive price point, enabling any deployment to enjoy a quick return on investment

Easy to Install

- Comes as a complete compact outdoor form factor offering unprecedented ease of installation
- Deployment tools include spectrum analyzer, antenna alignment and remote management configuration
- Non Line-of-Sight capability provided by Advanced Orthogonal Frequency Division Multiplexing (OFDM) along with 2x2 MIMO eases deployment in challenging areas
- Connects to all existing Tsunami[®] MP11, Tsunami[®] 8100 and Tsunami[®] 8200

PRODUCT MODELS

MP-825-CPE-50	Tsunami® MP 825 Customer Premise Equipment , 50 Mbps, MIMO 2x2, 15 dBi integrated antenna
MP-825-CPE-100	Tsunami® MP 825 Customer Premise Equipment , 100 Mbps, MIMO 2x2, 15 dBi integrated antenna

INTERFACES

WIRED ETHERNET	One auto MDI-X RJ45 10/100Mbps Ethernet with PoE in
WIRELESS PROTOCOL	WORP® (Wireless Outdoor Router Protocol) or WORP sync

RADIO & TX SPECS

MIMO	2x2 MIMO
MODULATION	OFDM with BPSK, QPSK, QAM16, QAM64
FREQUENCY	5.150 – 5.925 GHz (Subject to Country Regulations)
CHANNEL SIZE	40 MHz, 20 MHz, 10 MHz*, 5 MHz* channel bandwidths * Not applicable for DFS Band
DATA RATE	MCS 0 to 15 for High Throughput mode (6.5 – 300 Mbps) with Dynamic Data Rate Selection. BPSK, QPSK, 16-QAM and 64-QAM for legacy mode (6Mbps - 54Mbps)
TX POWER	Up to 26 dBm (dual chain)
TX POWER CONTROL	0 – 15 dB, in 0.5 dB steps. Automatic TPC with configurable EIRP limit
OTHER	Dynamic Channel Selection (DCS) based on interference detection, Dynamic Frequency Selection (DFS) based on radar signature, Automatic Transmit Power Control (ATPC) with EIRP limit support

RX SENSITIVITY (Per=10%)

Channel Size	40 MHZ	20 MHZ	10 MHz	5 MHz
MCS 0	-88 dBm	-92 dBm	-93 dBm	-94 dBm
MCS 7	-72 dBm	-74 dBm	-75 dBm	-77 dBm
MCS 8	-88 dBm	-91 dBm	-93 dBm	-94 dBm
MCS 15	-69 dBm	-71 dBm	-72 dBm	-75 dBm

ANTENNA

Integrated 15 dBi dual Polarized (H+V) panel antenna (14 dBi beyond 5.850 GHz)

MANAGEMENT

REMOTE	Telnet and SSH, Web GUI and SSL, TFTP, SNMPv3
SNMP	SNMP v1-v2c-v3, RFC-1213, RFC-1215, RFC-2790, RFC-2571, RFC-3412, RFC-3414, Private MIB
OTHER	Syslog, sFlow™ agent, SNMP and local time, Spectrum analyzer

SECURITY

ENCRYPTION	AES-CCM 128 bits
AUTHENTICATION	Internal MAC Address Control List, Radius based Authentication (with VLAN and QoS provisioning)

NETWORK

MODES	Bridging, Routing (RIP v2 and IP tunneling)
GATEWAY FEATURES	DHCP Server & relay, NAT with Std ALGs, PPPoE end point with Proxy DNS
THROUGHPUT	MP-825-CPE-50 - Up to 50 Mbps, MP-825-CPE-100 - Up to 100 Mbps

QoS

Asymmetric Bandwidth Control	Uplink and Downlink CIR Control "committed information rate" per service flow Uplink and Downlink MIR Control "maximum information rate" per service flow
Packet Classification Capabilities	802.1D/802.1Q/802.1p priority, IPTOS, VLAN ID, IP source/destination address, source/destination port, Ethernet source/destination address, IP protocol, and EtherType
Scheduling	Best Effort, Real Time Polling Services

VLAN

802.1Q: Management VLAN. Transparent, Access, Trunk and Mixed mode. QinQ double tagging

POWER CONSUMPTION

6 Watt typical (15 Watt max)

ENVIRONMENTAL SPECS

OPERATING TEMPERATURE	STORAGE TEMPERATURE	HUMIDITY, WATER & DUST PROOF, WIND LOADING
-40° to 55°C (-40° to 131°Fahrenheit)	-55° to 70°C (-67° to 158° Fahrenheit)	Max 100% relative humidity (non-condensing), IP67, 180 km/h (112 mph)

PHYSICAL SPECS

DIMENSIONS (PACKAGED)	DIMENSIONS (UNPACKAGED)	WEIGHT (PACKAGED)	WEIGHT (UNPACKAGED)
13.97 x 8.86 x 3.46 in (355 x 225 x 88 mm)	4.96 x 8.62 x 2.58 in (126 x 219 x 65.5 mm)	4.9 lbs (2.225 Kg)	2.1 lbs (0.950 kg)

SAFETY STANDARDS

UL 60950-1/22

PACKAGE CONTENTS

- One Tsunami® MP-825-CPE-50 with integrated antenna Or One Tsunami® MP-825-CPE-100 with integrated antenna
- One 20 W power injector and country specific power cord
- One Connector weatherproofing kit (Includes all recommended weatherproofing material)
- One Grounding kit
- One Quick Installation Guide
- One basic Pole mounting kit

MTBF & WARRANTY

>350,000 hours & 1-year on parts and labor; ServPak Extended Support available