

126-00086

Article Number: 126-00086

Domed Low Profile Mount Ties, 6.2" Long, Mounting Hole Diameter .25" - .26", PA66HS, Black, 500/pkg



Download drawing

Download spec sheet

Base Data

Local Order Number	126-00086
Type	T50SOSKSFT6.5S2-E
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"><li>• Dome provides a tight, rattle-free installation.</li><li>• Outside serrated strap has ribs designed for convoluted tubing.</li><li>• Dome acts as a seal to keep out dust and liquid.</li></ul>
Product Description	HellermannTyton's low profile push mount design provides an overall shortened length which assists in limiting protrusion on the opposing side of application surfaces. The rounded tip of the mount allows for a smoother surface in case of contact with surrounding components or human touch during service.
Fixation Method (FF)	Arrowhead
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Short Description	Domed Low Profile Mount Ties, 6.2" Long, Mounting Hole Diameter .25" - .26", PA66HS, Black, 500/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	50.0 lbs
Minimum Tensile Strength (N)	225 N
Length L (imperial)	6.2 "
Length L (metric)	157.0 mm
Width W (imperial)	0.18 "
Width W (metric)	4.6 mm
Height H (imperial)	0.58 "
Bundle Diameter min (imperial)	0.04 "
Bundle Diameter min (metric)	1.0 mm
Bundle Diameter max (imperial)	1.4 "
Bundle Diameter max (metric)	35.0 mm
Disc Diameter (imperial)	0.63 "
Disc Diameter (metric)	16.0 mm
Panel Thickness max. (imperial)	0.09 "
Panel Thickness max. (metric)	2.3 mm
Panel Thickness min. (imperial)	0.07 "
Panel Thickness min. (metric)	1.7 mm

Mounting Hole Diameter D (imperial)	0.25 - 0.26 "		
Mounting Hole Diameter D (metric)	6.3 - 6.7 mm		
Mounting Hole Diameter D min (imperial)	0.248 "	Mounting Hole Diameter D max (imperial)	0.264 "
			Thickness T (imperial)0.05 "
Mounting Hole Diameter D max (metric)	6.7 mm	Mounting Hole Diameter D min (metric)	6.3 mm
Thickness T (Metric)	1.3 mm		

Logistics and Packaging

Quantity per	bag
Package Quantity	500
Carton Quantity	5000 Pieces
Weight (Metric)	1.3 kg

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Conformity	Yes