

T30MR9C2



Article Number: 113-03019

Screw Mount Tie, 30lb, 6.3" Long, Max Bundle Diameter 1.3", #8 Screw PA66, Black, 100/pkg

 RoHS

 Download spec sheet

Base Data

Local Order Number	T30MR9C2
Type	T30MR9
Color	Natural (NA)
Features and Benefits	• Mount design secures firmly with any #8 Screw • Screw mount style creates low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Fixation Method (FF)	fixing hole
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Short Description	Screw Mount Tie, 30lb, 6.3" Long, Max Bundle Diameter 1.3", #8 Screw PA66, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135 N
Length L (Imperial)	6.3 "
Length L (Metric)	160.0 mm
Width W (Imperial)	0.14 "
Width W (Metric)	3.5 mm
Height H (Imperial)	0.17 "
Height H (Metric)	4.2 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.3 "
Bundle Diameter Max. (Metric)	32.0 mm
Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.3 mm
Thickness T (Imperial)	0.05 "
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces
Carton Quantity 5000 Pieces
Weight (Metric) 0.9 kg

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
CSA Certified No
Flammability UL94 V2
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS compliant (Article 4 - 1) Yes
Certification/Specification UL
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes