



The ComNet™ CopperLine® CopperKit CKFE1UTP Ethernet over UTP line consists of two single channel units in a single package containing cables and power supplies. They support 100Mbps Ethernet as well as Pass-through Power over Ethernet (PoE) over twisted pair cable (Cat5, UTP). The CKFE1UTP supports transmission distances of up to 3,000 feet (914m) at 10 Mbps, or 2,100 feet (640m) at 100 Mbps. The IEEE 802.3-compliant Ethernet electrical interface of these Ethernet extenders also meets the requirements for IEEE 802.3af PoE power, passing-through up to 30 watts of power per port to the powered device (PD). LED indicators confirm operating status of the device. Packaged in a rugged aluminum housing, these units are designed for desktop or stand-alone mounting. Environmentally hardened to the requirements of NEMA TS-1/ TS-2 for most out-of-plant applications, and true plug-and-play design ensures ease of installation and operation.

## FEATURES

- › Transmits individual Ethernet data channels with Pass-through PoE over standard UTP cable
- › Extends Ethernet up to 3,000 feet (914 m) over UTP
- › Extended temperature operation from -40C° to +75C°
- › Extended Pass-through PoE meets the IEEE 802.3af standard for Power over Ethernet
- › High-data rate, ideal for the high bandwidth requirements of Mega-pixel cameras, multiple IP cameras systems, and cameras requiring jumbo frame transmission
- › Symmetric Bandwidth provides consistent upload and download with virtually zero packet loss over the total usable distance
- › Type tested to RFC-2544 TCP/IP network bandwidth packet transmission standards
- › User-selectable data rate for maximum bandwidth and transmission distance utilization
- › Complies with all major IEEE standards and RFC network protocols for UDP, TCP/IP, HTTP/HTTPs
- › Designed for use in harsh operating environments: Fully compliant with the environmental requirements of NEMA TS-1/TS-2 and the Caltrans specification for traffic signal Control equipment
- › Aluminum housing
- › Designed and manufactured in the USA
- › Lifetime Warranty

## APPLICATIONS

- › Retrofit existing analog CCTV installations to Ethernet-based systems
- › CCTV systems for Casinos, airports, school campuses

## SPECIFICATIONS

## Electrical

Ethernet Interface:	10/100BaseT
Ethernet Data Rate	DIP-switch selectable 10/100Mbps Full data rate / full duplex up to the maximum rated distance
Transmission distance	UTP Cable <sup>1</sup> , 3,000 feet (914m) at 10BaseT, or 1,800 feet (548m) at 100BaseT
Operating Power	12 VDC, 24 VAC or POE af @ 150mA (max.)
Status Indicating LEDs	- Operating Power - Ethernet: Traffic - Link Extended Ethernet Traffic
Connectors	Ethernet Interface: RJ-45 Extended Interface: RJ-45 Operating Power: Terminal Block
RFC	2544 TCP/IP Packet Transmission
Standards Compatibility	IEEE 802.3af PoE, RFC: 768 UDP, 2068 HTTP, 793 TCP 791 IP, 1783 TFTP, 894 IP over Ethernet
Jumbo Frame	Supported


## Mechanical

Size (H x W x L)	1.15 x 1.6 x 3.73 in (3.0 x 4.0 x 9.5 cm)
Weight	< 1lb (0.45 kg)
Case Material	Aluminum

## Environmental


MTBF	> 100,000 hours
Operating Temp	-40°C to +75°C
Storage Temp	-40°C to +80°C
Relative Humidity	0 to 95%, non-condensing

[1] Distance figures are based on a 50V PSE PoE power source, and external power supplies for the extenders. Distance figures are obtained using in-house testing mirroring installations. Factors such as coaxial cable quality, the number of connectors in the cable run, the use of PoE, and environmental conditions encountered within the installation may affect the actual transmission distance, and should be taken into consideration.



MADE IN THE  
**USA**

## DIMENSIONS



## ORDERING INFORMATION

Part Number	Description	Maximum Distance†
CKFE1UTP	1 Port UTP/Twisted Pair Ethernet Extender	3,000 ft (914 m)
Accessories	12 VDC wall-mount power supply (one each provided with each extender unit)	

Tested and certified by an independent laboratory for full compliance with the environmental requirements (ambient operating temperature, mechanical shock, vibration, humidity with condensation, high-line/low-line voltage conditions, and transient voltage protection) of NEMA TS-1/TS-2 and the Caltrans Specification for Traffic Signal Control Equipment.

Low Power Consumption