


10/100 Mbps Ethernet Electrical to Optical media converter







The ComNet™ CNFE2MC Ethernet and CNFE22MC media converters are designed to transmit and receive 10/100 Mbps data over optical fiber through user selectable SFP options. These models require the ordering of sold-separately interchangeable SFP modules for fiber type, distance and connectors. The CNFE2MC transmits and receives a single channel of Ethernet data and the CNFE22MC transmits and receives two independent channels in one unit. The electrical interface will Auto-Negotiate to a 10 Mbps, or 100 Mbps Ethernet rate without any adjustments. The optical interface operates at a 100 Mbps Ethernet rate. Both are environmentally hardened to operate in extreme temperatures. LED indicators are provided for confirming equipment operating status. Packaged in the exclusive ComNet ComFit housing, the CNFE2MC and CNFE22MC units may be either wall or rackmounted, or may be DIN-rail mounted by the addition of ComNet model DINBKT1 adaptor plate.

Applications

- 10/100 Mbps Ethernet Media Converter
- High-Performance Computer Links

Features

- 10/100 Mbps Ethernet
- 10/100 BASE-T/TX electrical port
- 100 BASE-FX optical port
- Electrical port supports Auto-Negotiation for 10 Mbps or 100 Mbps, full duplex or half duplex data.
- Optical port supports 100 Mbps full duplex data
- Automatic MDI/MDI-X crossover
- Distances up to 80 km with optional SFPs
- Designed to meet full compliance with the environmental requirements (ambient operating temperature, mechanical shock, vibration, humidity with condensation, high-line/low-line voltage conditions and transient voltage protection) of NEMA TS-1/TS-2 and the Caltrans Specification for Traffic Signal Control Equipment.
- Uses interchangeable SFP for fiber type, distance and connector (Ordered separately)
- Voltage transient protection on all power and signal input/output lines provides unconditional protection from power surges and other voltage transient events.
- No in-field optical adjustments required
- CNFE2MC and CNFE22MC are hot-swappable rack modules
- CNFE2MC and CNFE22MC are interchangeable between standalone or rack mount use - ComFit
- LED Indicators
- IEEE 802.3 compliant
- Lifetime Warranty

SFP = Small Form-Factor Pluggable Module

specifications

DATA

Data Rate:

Data Interface:

Ethernet 10/100 Mbps IEEE 802.3 Compliant

Full Duplex or Half Duplex Electrical

Port/Full Duplex Optical Port

FIBERS* SFP Dependent

FIBER CONNECTORS Requires selection of sold-separately SFP

modules. See ComNet data sheet for number and description of SFP modules

CONNECTORS

Power: Terminal Block Electrical: RJ45

LED INDICATORS - Optical Link/Data Activity

- Power

ELECTRICAL & MECHANICAL

ower:

Surface Mount: 8-15 VDC @ 220 mA Rack Mount: From Rack

Number of Rack Slots:

Current Protection: Automatic Resettable

Solid-State Current Limiters

Circuit Board: Meets IPC Standard

Size (in./cm) (L×W×H)

Standard Size 6.1 x 5.3 x 1.1 in.,

(15.5 x 13.5 x 2.8 cm)

Small Size 3.3 x 2.5 x 1.1 in., (8.4 x 6.4 x 2.8 cm)

Shipping Weight: <2 lbs./0.9 kg

ENVIRONMENTAL

 MTBF:
 >100,000 hours

 Operating Temp:
 -40° C to +75° C

 Storage Temp:
 -40° C to +85° C

Relative Humidity: 0% to 95% (non-condensing)[†]

* Multimode fiber needs to meet or exceed fiber standard ITU-T G.651. Single mode fiber needs to meet or exceed fiber standard ITU-T G.652

[†] May be extended to condensation conditions














NOTE: This product requires a fiber installation with a minimum 30 dB connector return loss.

The use of Super Polish Connectors is recommended.

Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J

In a continuing effort to improve and advance technology, product specifications are subject to change without notice.



T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET

8 TURNBERRY PARK ROAD | GILDERSOME | MORLEY | LEEDS, UK LS27 7LE T: +44 (0)113 307 6400 | F: +44 (0)113 253 7462 | INFO-EUROPE@COMNET.NET