



The NetWave® pre-configured point-to-point industrially hardened wireless Ethernet Transmission kit that allows Ethernet data to be transmitted between a Client remote location and the Access Point or head end. The NWK1 and NWK2 support up to 95 Mbps throughput due to MIMO technology. An easy to read LED array displays unit operational status along with received signal strength ensuring optimal installation and operation. The units can be powered by an IEEE 802.3af PoE compliant device or through the supplied power injection module. The NWK1 is FCC certified for use in North America and the NWK2 is ETSI, DFS and TPC certified for use in the European Union. Each kit contains two passive power injectors, power supplies and mounting hardware.

## FEATURES

- › Lifetime Warranty
- › Pre-configured Access Point and Client units for quick setup
- › Up to 95 Mbps Throughput
- › 802.11a/n Compliant
- › Distances up to 2 mi (FCC) or 2km (ETSI)
- › Powered by the included power injection module or by an IEEE802.3af PoE compliant device
- › Environmentally Hardened -40° to +75°C
- › Meets class IP67 dust and water immersion protection standards
- › ETSI Standards (EU Region only):
  - DFS Dynamic Frequency Selection
  - TPC Transmit Power Control
- › Secure transmission: WPA2 - AES or TKIP encryption
- › ComNet Antenna alignment feature eases installation and setup
- › RF Spectrum Survey Tools

- › Antenna Alignment Tools
- › LED array displays unit operational status along with received signal strength

## APPLICATIONS

- › Simple to deploy and cost-effective alternative to physical connections to Ethernet edge equipment
- › Integration of Ethernet where right-of-way issues mandate wireless communications
- › ITS traffic signalization networks and Video Detection Systems (VDS)
- › ITS roadside and city center CCTV surveillance, and surveillance of high-value or mission-critical assets
- › Wireless communications in manufacturing, petrochemical refineries, wastewater treatment facilities, and other industrial automation and control applications operating in harsh or out-of-plant environments
- › Electrical substation video and perimeter surveillance

SPECIFICATIONS

Wireless Radio

EIRP	NW1 (FCC): Up to +36dBm for point to multipoint deployments, +45dBm for point to point deployments with MAC-lock feature enabled NW2 (ETSI): +30dBm
RF Output	+26dBm Rated Transmitter
Operational Frequency	5500GHz - 5825GHz, Region-dependent. Not all frequencies are supported in all regions. Contact ComNet for frequencies supported in your region.
Bandwidths	10, 20, and 40MHz

Standard Internal Antenna

Antenna	Internal 19dBi Dual Polarized Directional
Gain	19dBi
Azimuth	17° Horizontal/Vertical
Elevation	17° Horizontal/Vertical

Connectors

10/100 Ethernet	2 × RJ-45, Sealed Cable Gland
-----------------	-------------------------------

Indicating LEDs

Power On, Ethernet Link, Signal Strength



Software Features

Addressing	Static IP / DHCP Client / DHCP Server
SNMP	V3
Spanning Tree Protocol support	
Telnet Server	
Syslog	
802.1x Port-Based Network Access Control	
NTP Client	
User-Configurable Watchdog and Auto-Reboot Mechanism	
Multi-Level Configuration and Monitoring Login Accounts	
User Configurable Long Range Parameters	

Power

Operating Voltage	+36 VDC @ 153mA 48 to 57 VDC @ 115mA
Power Consumption	5.5W Max
PD Power	IEEE802.3af PD compliant

Mechanical

Size (L × W × H)	10.6 × 10.6 × 2.9 in (27 × 27 × 7.5 cm)
Shipping Weight:	<2lbs/0.9kg

Environmental

MTBF	>100,000 hours
Operating Temp	-40° C to +75° C
Storage Temp	-40° C to +85° C
Relative Humidity	5% to 95%

Note: In a continuing effort to improve and advance technology, product specifications are subject to change without notice.

ORDERING INFORMATION

Part Number	Description
NWK1	Industrially Hardened Point-to-Point Wireless Ethernet Kit, distances up to 2 mi/3.2 km. Consult ComNet tech support for system designs beyond 2 mi/3.2 km. FCC certified for North America
NWK2	Industrially Hardened Point-to-Point Wireless Ethernet Kit, distances up to 2 km/1.25 mi, ETSI certified for European Union
Included Accessories	2 × Power Kit with Power Supply and Passive Power Injector 2 × Mounting Hardware Kit
Options	NWBKT - Articulating Wall Mount Bracket (Sold Separately)

TYPICAL APPLICATION

