

PowerVerter APS INT 2000W 12VDC 230V Inverter/Charger with Pure Sine Wave Output, Hardwired

MODEL NUMBER: **APSX2012SW**



Description

Provide Pure Sine Wave power for all your alternative energy needs with the Tripp Lite APSX2012SW. This inverter/charger supplies 2000 watts of continuous 230V AC power. Reliable large transformer design and frequency control powers resistive loads such as refrigerators, motors, pumps, compressors and laser printers as well as electronic loads like TV's, Computers, power tool and battery chargers. The 3-stage charging system will properly charge and maintenance your vehicle battery or separate battery bank. The charge rate is selectable so you can use a variety of battery sizes as well as multiple batteries to fit your run time requirements.

Features

- Pure sine wave output
- Continuous output inverter and high power battery charger
- Quiet, high efficiency operation, high surge capacity and low idle current
- Supply energy to various loads such as resistive load
- Seamless transfer switching
- Load sensing adjustable
- Unlimited back up time with user supplied batteries

Highlights

- 12V DC or 230V AC input; 230V, 50 Hz output (hardwired)
- 2000 watts continuous output, 4000 watts peak output
- Selectable 6/60 amp wet/dry cell battery charger
- Pure sine wave output
- Quiet, high efficiency operation, high surge capacity and low idle current
- Seamless transfer switching

Applications

- Versatile inverter/charger system with seamless transfer switching serves as an automotive inverter for RVs, over-the-road trucking, conversion vans and fleet service vehicles; a standalone alternative power source for off-grid, alternative energy or export applications and as an uninterruptible power supply (UPS) for items compatible with a 10 millisecond transfer time.

Package Includes

- APSX2012SW Inverter/Charger
- Instruction manual with warranty information

Specifications

OVERVIEW	
Style	Heavy-duty with built-in battery charger
OUTPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Frequency Compatibility	50 Hz
Output Receptacles	Hardwire
Output (Watts)	2000
Continuous Output Capacity (Watts)	2000
Peak Output Capacity (Watts)	4000
Output Nominal Voltage	230V
Output Voltage Regulation	LINE POWER (AC): Maintains 230V nominal sine wave output from line power source. INVERTER POWER (AC): Maintains sine wave output voltage of 230 VAC (+/-5%).
Output Frequency Regulation	50 Hz (+/- 0.3 Hz)
Overload Protection	Includes 15A input breaker dedicated to the charging system and 15A output breaker for AC output loads
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	DC INPUT: Requires 12VDC input source capable of delivering 240A for the required duration (when used at full continuous capacity - DC requirements increase during OverPower and DoubleBoost operation). For automotive applications, professional hardwire installation with 400A minimum battery system fusing is recommended.
Maximum Input Amps / Watts	DC INPUT: Full continuous load - 240A at 12VDC. AC INPUT: 17 amps at 230VAC with full inverter and charger load (8.7A max charger-only / combined input load to support charger and AC output is automatically controllable to 66%-33%-0% based on AC output loading using the charger limiting set points - see manual for setting instructions)
Input Connection Type	DC INPUT: Set of 2 DC bolt-down terminals. AC INPUT: Hardwire via built in junction box with cover plate
Voltage Compatibility (VAC)	230
Voltage Compatibility (VDC)	12
BATTERY	
Expandable Battery Runtime	Runtime is expandable with any number of user supplied wet or gel type batteries
DC System Voltage (VDC)	12
Battery Pack Accessory (Optional)	98-121 sealed lead acid battery (optional)
Battery Charge	Selectable 6/60 amp
VOLTAGE REGULATION	
Brownout Correction	Brownout transfer point - 170V (+/- 3%)
Severe Brownout Correction	Brownout reset point - 180V (+/- 3%)
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Display inverter status, charger status as well as battery voltage status
Switches	The inverter provides an RJ-45 port for optional APSRMSW remote control. RJ-45 port operates with standard RS-485 interface (APSRMSW sold separately)
Audible Alarm	Audible Status indicators (see manual)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Weight (lbs.)	46
Shipping Weight (kg)	20.9
Unit Dimensions (hwd / in.)	7.25 x 8.75 x 21.75
Unit Dimensions (hwd / cm)	18.41 x 22.22 x 55.24
Unit Weight (lbs.)	51.16
Unit Weight (kg)	23.21
Cooling Method	Multi-speed fan
Material of Construction	Powder coated steel
Receptacle Color	Gray
Form Factors Supported	Mounting slots enable permanent placement of inverter on any horizontal surface (see manual for additional mounting information)
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
LINE / BATTERY TRANSFER	
Transfer Time (Line Power to Battery Mode)	10 milliseconds
Low Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 144V (user adjustable to 163, 182, 201V - see manual)
High Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 259V (user adjustable to 264 - see manual)
SPECIAL FEATURES	
Load Sensing	150W ~ 220W
Remote Control Capability	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty