

AVR Series 230V 550VA 300W Ultra-Compact Line-Interactive UPS with USB port, CEE7/7 Schuko Outlets

MODEL NUMBER: **AVRX550UD**



Highlights

- 550VA ultra-compact 230V line interactive UPS
- Corrects brownouts and overvoltages from 159V to 282V
- 4 UPS battery supported outlets, 4 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable, 99% efficient
- CEE 7/7 Schuko input & output connections

Package Includes

- AVRX550UD UPS System
- USB Cable
- Quick start guide

Description

Tripp Lite's AVRX550UD Ultra-Compact Line Interactive UPS offers complete power protection for desktop PCs, network workstations and a wide variety of professional and consumer electronic devices. Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures. Automatic Voltage Regulation / AVR power conditioning maintains smooth, continuous operation of connected equipment during brownouts and overvoltages. Surge-only outlets offer convenient protection for printers and other desktop accessories not requiring battery support. AC and dataline surge suppression prevents connected equipment damage. USB communications port supports built-in power management and auto-shutdown features of Windows and Mac OS X or full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

Features

- AVRX550UD ultra-compact 230V line interactive UPS offers complete AC power protection from blackouts, brownouts and transient surges
- 550VA / 300 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Automatic Voltage Regulation / AVR corrects extended brownouts and overvoltages from 159 to 282V, without using battery power
- 3 minutes runtime at 100% load (300 watts), 9.7 minutes runtime at 50% load (150 watts)
- 20 minutes runtime for a desktop computer system consuming 80 watts continuous
- 8 total CEE7/7 SCHUKO outlets
- 4 UPS battery backup outlets, plus 4 additional surge-only outlets
- CEE7/7 SCHUKO input connection with 1.8m line cord
- Network grade AC surge and lightning protection is available from all outlets; Built-in data line surge suppression protects a single dialup or DSL line
- 99% line mode efficiency rating uses less energy and BTU emissions



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment, ideal for unattended kiosk applications
- Hot swappable user battery replacement
- Space saving, ultra-compact housing with support for wall-mount, desktop or floor placement

Specifications

| OUTPUT | |
|--|---|
| Output Volt Amp Capacity (VA) | 550 |
| Output Watt Capacity (Watts) | 300 |
| Nominal Output Voltage(s) Supported | 230V |
| Nominal Voltage Details | 230V nominal inverter output voltage |
| Frequency Compatibility | 50 / 60 Hz |
| Output Voltage Regulation (Line Mode) | +8%, -21% |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| Output Receptacles | (8) CEE7/7 |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | PWM sine wave |
| INPUT | |
| Rated input current (Maximum Load) | 10A |
| Nominal Input Voltage(s) Supported | 230V AC |
| UPS Input Connection Type | CEE 7/7 Schuko |
| UPS Input Cord Length (ft.) | 6 |
| UPS Input Cord Length (m) | 1.8 |
| Input Phase | Single-Phase |
| BATTERY | |
| Full Load Runtime (min.) | 3 min. (300w) |
| Half Load Runtime (min.) | 9.7 min. (150w) |
| DC System Voltage (VDC) | 12 |
| Battery Recharge Rate (Included Batteries) | Less than 15 hours from 10% to 90% |
| Battery Access | Battery access door |
| Battery Replacement Description | Hot-swappable, user replaceable batteries |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| VOLTAGE REGULATION | |
|---|--|
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 159 to 282VAC |
| Overvoltage Correction | Input voltages between 245 and 282 are reduced by 12% |
| Undervoltage Correction | Input voltages between 159 and 205 are boosted by 14% |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Combination switch controls on/off power status and self-test operation |
| Audible Alarm | Audible alarm indicates power-failure and overload status |
| LED Indicators | 2 LEDs indicate power status and overload/check battery status |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 320 |
| UPS AC Suppression Response Time | Instantaneous |
| UPS Dateline Suppression | 1 line TEL/DSL (1 in / 1 out) |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Installation Form Factors Supported with Included Accessories | Ultra-compact desktop |
| Primary Form Factor | Desktop |
| UPS Power Module Dimensions (hwd, in.) | 4.73 x 11 x 6 |
| UPS Power Module Dimensions (hwd, cm) | 12 x 27.9 x 15.2 |
| UPS Power Module Weight (lbs.) | 11.5 |
| UPS Power Module Weight (kg) | 5.2 |
| UPS Shipping Dimensions (hwd / in.) | 7.3 x 14.2 x 9.53 |
| UPS Shipping Dimensions (hwd / cm) | 18.5 x 36.1 x 24.2 |
| Shipping Weight (lbs.) | 12.3 |
| Shipping Weight (kg) | 5.6 |
| UPS Housing Material | ABS |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius. |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius. |
| Relative Humidity | 0 to 95%, non-condensing |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|---|
| AC Mode BTU / Hr. (Full Load) | 16 |
| AC Mode Efficiency Rating (100% Load) | 99% |
| COMMUNICATIONS | |
| Communications Interface | USB |
| PowerAlert Software | Free download from www.tripplite.com |
| Communications Cable | USB interface cable included |
| WatchDog Compatibility | Supports Watchdog application, OS and hard-reboot restart options for remote applications |
| Network UPS Tools Compatibility | NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 5 milliseconds (line to battery mode) / 1 millisecond (battery to line mode) |
| Low Voltage Transfer to Battery Power (Setpoint) | 159 |
| High Voltage Transfer to Battery Power (Setpoint) | 282 |
| SPECIAL FEATURES | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| High Availability UPS Features | hot-swap batteries |
| Green Energy-Saving Features | Greater than 95% efficiency - GREEN UPS |
| CERTIFICATIONS | |
| UPS Certifications | CE; Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances) |
| UPS Certification Details | IEC 62040, IEC 60950, EN 62040, GS MARK |
| WARRANTY | |
| Product Warranty Period (International) | 2-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.