

Isobar 10-Outlet Home/Business Theater Surge Protector, 8-ft. Cord, 3840 Joules

MODEL NUMBER: HT10DBS



Description

Tripp Lite's HT10DBS Isobar Home/Business Theater Surge Suppressor provides premium protection--3840 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for medium-to-large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 10 outlets (with transformer spacing and plug-in safety covers), 3-line 2.2 GHz gold coaxial protection, 1-line tel/modem protection and 1-line network (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$500,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes all-metal housing, color-coordinated outlet/plug labels, three diagnostic LEDs, 8-ft. cord with a right-angle plug, 6-ft. gold coax cable, 6-ft. phone cord and 6-ft. network cable.

Features

- 3840 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$500,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- Isolated Filter Banks eliminate interference between connected components
- All-metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely spaced outlets accommodate up to 6 transformers
- Four plug-in safety covers protect against accidental contact with unused outlets
- 3 sets of 2.2GHz gold coaxial connectors (with included 6-ft. gold coax cable) safeguard components on cable, satellite and antenna line
- 1-line tel/modem and 1-line network (100BaseT, high-speed) surge protection (with included 6-ft. phone cord and 6-ft. network cable) safeguards personal video recorders (PVRs) on up to two lines simultaneously.
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 3 diagnostic LEDs alert user to protection, line power and ground status

Highlights

- 10 outlets/8-ft cord
- 3840 joule rating—more joules mean more protection!
- All-metal housing with diagnostic LEDs
- Isolated filter banks remove damaging line noise
- 3-line coaxial, single-line tel/modem and single-line network surge protection
- \$500,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Perfect for medium-to-large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more.

Package Includes

- HT10DBS Home/Business Theater Surge Protector
- 6-ft. gold coax cable
- 6-ft. phone cord
- 6-ft. network cable
- Instruction manual with warranty information

- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- Color-coordinated outlet/plug labels

Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(10) 5-15R
Output (Watts)	1440
Circuit Breaker (amps)	12
Transformer Accommodation	Accommodates 6 transformers
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right-angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm line power, protection and ground status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression



Clamping Voltage (RMS)	140V
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Up to 60 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Unit Dimensions (hwd / in.)	14.25 x 2.25 x 3.5
Unit Dimensions (hwd / cm)	36.2 x 2 x 5.7
Unit Weight (lbs.)	3.5
Unit Weight (kg)	1.6
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting slots allow desk or wall mounting
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	Distance between horizontal standard outlets = 39.45mm; Distance between horizontal transformer outlets = 53mm; Distance between vertical outlets = 38.76mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 355.09mm; Distance between vertical tabs = 58.17mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition requirements by ETL
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 Ultimate Lifetime Insurance
---	---

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.