

Duplex Multimode 62.5/125 Fiber Patch Cable (ST/ST), 15M (50-ft.)

MODEL NUMBER: **N302-15M**



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with ST/ST connectors.

Package Includes

- 15-meter (50-ft.) Duplex MMF Cable ST/ST 62.5/125 Fiber

Description

Tripp Lite's 15-meter multimode duplex fiber optic ST/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has ST connectors on each end, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 15-meters(50ft) Connectors: 2 ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze.
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Network Speed	1Gbps
Style	Fiber Optic



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Fiber Type	62.5/125 - OM1
Model Type	ST/ST
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC
INPUT	
Cable Length (ft.)	49
Cable Length (m)	15
PHYSICAL	
Color	Orange
CONNECTIONS	
Connector A	ST
Connector B	ST
Number of Connectors	4
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.