

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Duplex Multimode 62.5/125 Fiber Patch Cable (SC/ST), 5M (16-ft.)

MODEL NUMBER: N304-05M



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

 Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/ST connectors

Package Includes

 5-meter duplex MMF cable ST/SC 62.5/125 fiber

Description

Tripp Lite's 5-meter multimode duplex fiber optic SC/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has ST to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 5-meters(16.4ft) Connectors: 2 ST to 2 SC connectors
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- · Color coded shrouds identify transmit and receive
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1
Model Type	SC/ST



Cable Types	MULTIMODE 62.5/125 FIBER OPTIC	
INPUT		
Cable Length (ft.)	16	
Cable Length (m)	5	
PHYSICAL		
Color	Orange	
CONNECTIONS		
Connector A	SC	
Connector B	ST	
Number of Connectors	4	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.