

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/SC), 25M (82-ft.)

MODEL NUMBER: **N316-25M**



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/LC connectors

Package Includes

- 25 meter (80ft) Duplex MMF Cable LC/SC 62.5/125 Fiber

Description

Tripp Lite's 25-meter (80ft) multimode duplex fiber optic SC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 25-meter (80ft) Connectors: 2 SC/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)

Specifications

OVERVIEW	
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1
Model Type	LC/SC
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC
INPUT	
Cable Length (ft.)	82



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	25
PHYSICAL	
Color	Orange
CONNECTIONS	
Connector A	LC
Connector B	SC
Connector C	LC
Connector D	SC
Number of Connectors	4
CERTIFICATIONS	
Certifications	ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.