

Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Green, 50-ft.

MODEL NUMBER: N201-050-GN



Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces cross-talk and return loss
- IEC 802.3ab
- PVC 4-pair solid UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

Package Includes

50-ft. Cat6 Green Gigabit Patch Cord Snagless Molded

Description

With Tripp Lite's Category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags.

Features

- Length: 50 ft./Color: Green/Connectors: RJ45 male
- . Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- · High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation

Specifications

OVERVIEW		
Style	Cat6/6e/6a	
Model Type	Snagless	
Cable Types	CAT6	
INPUT		
Cable Length (ft.)	50	
Cable Length (m)	15.24	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL		
Color	Green	
CONNECTIONS		
Connector A	RJ45 (MALE)	
Connector B	RJ45 (MALE)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.