

Duplex Multimode 62.5/125 Fiber Patch Cable (MTRJ/LC), 2M (6-ft.)

MODEL NUMBER: N314-02M



Highlights

- Premium PVC 62.5/125μm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

 Any fiber optic hardware or NIC card requiring multimode duplex cable with MT-RJ/LC connectors

Package Includes

2-meter Duplex MMF MTRJ/LC
 62.5/125 Fiber cable

Description

Tripp Lite's 2-meter multimode duplex fiber optic MTRJ/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has MTRJ to LC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 2-meter/connectors: MTRJ to (2) LC
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1
Model Type	MTRJ/LC
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT		
Cable Length (ft.)	7	
Cable Length (m)	2	
PHYSICAL		
Color	Orange	
CONNECTIONS		
Connector A	MTRJ	
Connector B	LC	
Connector C	LC	
Number of Connectors	3	
CERTIFICATIONS		
Certifications	ROHS	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.