

10/100 SC Multimode Media Converter, 550M, 850nm

MODEL NUMBER: **N784-001-SC-MM**



Highlights

- Extends a 100Mb Ethernet signal up to 550M over Multimode Fiber Optic Cable
- Auto detects Full/Half Duplex Transfer Mode

System Requirements

- 10/100 Ethernet Network
- Multimode SC Fiber cable

Package Includes

- 10/100 SC Multimode Media Converter, 550M, 850nm
- AC Power Adapter
- User Manual

Description

Tripp Lite's N784-001-SC-MM 10/100 to Multimode Media Converter (RJ45 to SC) is an economical way to extend the distance of network nodes up to 550 Meters by converting Cat5e UTP cables to Multimode Fiber Optic. The Media Converter features automatic MDI/MDI-X configuration, and the UTP port senses the network speed automatically. Auto-detects half or full duplex operation on the fiber port. Power supplied by small form factor AC adapter.

Features

- 10/100 UTP to SC Multimode Fiber converter
- Up to 550M (1800ft) range
- Auto-detects Full / Half Duplex Transfer Mode
- Auto Negotiation MDI / MDI-X
- 6 performance monitoring LEDs
- 850nm wavelength
- Small, compact design

Specifications

OVERVIEW	
Chromebook Compatible	No
AC Adapter	Input: 100-240V, 50/60Hz; Output: 5V, 1.2AMP
Model Type	Adapters
PHYSICAL	
Unit Dimensions (hwd / in.)	1.00 x 4.70 x 2.75
Unit Weight (lbs.)	1.00



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
CONNECTIONS	
Connector A	RJ45 (FEMALE)
Connector B	SC (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.