

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 10M (33-ft.)

MODEL NUMBER: **N318-10M**



Highlights

- Premium 62.5/125 duplex (zipcord) fiber patch cable - 10 m
- Ideal for LAN applications
- Glass fiber composition
- LC/ST connectors

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/ST connectors

Package Includes

- 10-meter duplex MMF LC/ST 62.5/125 fiber cable

Description

Tripp Lite's 10-meter multimode duplex fiber optic LC/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to ST connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-meters/Connectors: 2 LC/ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1
Model Type	LC/ST
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	33
Cable Length (m)	10
PHYSICAL	
Color	Orange
CONNECTIONS	
Connector A	LC
Connector B	ST
Connector C	LC
Connector D	ST
Number of Connectors	4
CERTIFICATIONS	
Certifications	ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.