

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 50M (164-ft.)

MODEL NUMBER: **N318-50M**



Highlights

- Premium 62.5/125 duplex (zipcord) fiber patch cable
- Ideal for LAN applications
- Glass fiber composition

System Requirements

Any fiber optic hardware or NIC card requiring multimode duplex cable with ST/LC connectors

Package Includes

- 50M duplex MMF LC/ST 62.5/125 fiber cable

Description

Tripp Lite's 50M multimode duplex fiber optic ST/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to ST connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 50M / Connectors: ST and LC Duplex connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

| OVERVIEW | |
|---------------|--------------------------------|
| Network Speed | 1Gbps |
| Style | Fiber Optic |
| Fiber Type | 62.5/125 - OM1 |
| Model Type | LC/ST |
| Cable Types | MULTIMODE 62.5/125 FIBER OPTIC |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| INPUT | |
|-------------------------------------|---------------------------|
| Cable Length (ft.) | 164 |
| Cable Length (m) | 50 |
| PHYSICAL | |
| Color | Orange |
| CONNECTIONS | |
| Connector A | LC DUPLEX (MALE) |
| Connector B | ST DUPLEX (MALE) |
| CERTIFICATIONS | |
| Certifications | RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.