

## VGA Coax Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M), 100-ft.

MODEL NUMBER: **P502-100**



### Description

Tripp Lite's 100 foot SVGA/VGA monitor replacement cable ( Male-Male ) is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors
- Resolutions up to 2048 x 1536

## Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Display Style	Cable
Model Type	VGA
Cable Types	MONITOR
INPUT	

### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- Resolutions up to 2048 x 1536

### System Requirements

- Monitor with removable HD15 cable
- Switchbox w/HD15F to CPU w/HD15F

### Package Includes

- 100-ft. SVGA/VGA Monitor Cable HD15M to HD15M Gold Connectors w/ RGB Coax



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	100
Cable Length (m)	30.48
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.