

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 10M (33-ft.)

MODEL NUMBER: N320-10M-RD



Description

Tripp Lite's Red, 10-meter multimode duplex micron fiber optic LC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC connectors on each end, a PVC jacket, and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications. Ideal for color coding the cable plant.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 10 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) and OFNR rated

Specifications

OVERVIEW	
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1
Model Type	LC/LC
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC
INPUT	
Cable Length (ft.)	33

Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber with Red jacket
- Length: 10 meter Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical)

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

Package Includes

- 10M Duplex MMF Cable LC/LC 62.5/125 Micron Fiber Red Jacket



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	10
PHYSICAL	
Color	Red
CONNECTIONS	
Connector A	LC
Connector B	LC
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.