

## Duplex Singlemode 8.3/125 Fiber Patch Cable (LC/ST), 3M (10-ft.)

MODEL NUMBER: **N368-03M**



### Description

Tripp Lite's 3-meter, single mode duplex fiber optic LC/ST patch cable is manufactured from 8.3/125 zipcord fiber. The cable has LC connectors on one end, ST connectors on the other, a PVC jacket, and is FDDI and OFNR rated. Duplex single mode fiber is most commonly used in LAN applications.

### Features

- Tripp Lite's 3-meter, single mode duplex fiber optic LC/ST patch cable is manufactured from 8.3/125 zipcord fiber
- The cable has LC connectors on one end, ST connectors on the other, a PVC jacket, and is FDDI and OFNR rated
- Duplex single mode fiber is most commonly used in LAN applications

## Specifications

OVERVIEW	
Clad Diameter	125 Micron
Core Diameter	8.3 Micron
Number of Fibers	2
Style	Fiber Optic
Fiber Type	8.3/125
Model Type	LC/ST
Cable Types	SINGLEMODE 8.3/125 FIBER OPTIC
INPUT	
Cable Length (ft.)	10

### Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

### Applications

- Networking equipment that requires single mode fiber optic patch cables

### System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with LC/SCconnectors

### Package Includes

3 - Meter Duplex Single mode Fiber patch cable, LC/ST



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (m)	3
<b>PHYSICAL</b>	
Color	Yellow
<b>CONNECTIONS</b>	
Connector A	LC
Connector B	ST
Number of Connectors	4
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.