

## Smart Pro Tower UPS System - NAFTA assembled version of SMART1050

MODEL NUMBER: **SM1050NAFTA**



### Description

Tripp Lite's SM1050NAFTA intelligent, line interactive UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 23 minutes half load runtime and 8 minutes at full load during power failures. 1050VA/705 watt power handling capability supports a variety of networking, telecom and various other application types, including the support of multiple network workstations. Includes a total of 6 UPS supported outlets. Supports remote monitoring of UPS and site power conditions via built-in USB monitoring port. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level. Wall mountable with UPSWM wallmount bracket. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges. Attractive, small-footprint tower housing uses less than 53 square inches of floor or desktop space. \$250,000 [connected equipment insurance](#).

### Features

- 1050VA/705 watt power handling capability supports a variety of networking, telecom and various other application types
- Built-in voltage regulation and battery support prevents equipment damage, data loss and downtime
- Large internal batteries offer 23 minutes half load runtime and 8 minutes at full load during power failures
- Automatic Voltage Regulation (AVR) circuits with two boost and one voltage reduction level maintains usable 120V nominal output over an input voltage range of 75-147V
- Includes a total of 6 NEMA5-15R outlets
- Includes 1 USB communications port for remote monitoring of UPS status and site power conditions
- Communications port enables safe unattended shutdown without data loss during extended power failures
- Communications port supports messaging of UPS and line power status, including on-battery, low-battery, power-restored, AC line voltage, DC battery voltage and battery capacity
- Communications port supports timed inverter shutoff after unattended shutdown, activate self-test and 10 second reboot of connected equipment
- PowerAlert UPS monitoring and unattended shutdown software with complete cabling included
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Notification of system status via 5 LEDs and multi-function audible alarms

### Highlights

- 1050VA line interactive tower UPS system
- Enhanced USB communications port
- Corrects brownouts and overvoltages from 75 to 147V
- 6 outlets
- \$250,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

### Package Includes

- SMART 1050 UPS System
- USB monitoring cable
- PowerAlert unattended shutdown and UPS/Power monitoring software
- Instruction manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Wall mountable with UPSWM wallmount bracket
- Attractive small footprint beige tower housing uses less than 53 square inches
- Hot-swappable/user replaceable batteries allow on-site battery replacement
- Cold start capability enables UPS turn-on in battery mode during blackout conditions
- UL (USA), cUL (Canada), NOM (Mexico), Class B (Emmissions)
- \$250,000 [Ultimate Lifetime Insurance](#)

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1050
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	705
Power Factor	0.7
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) 5-15R
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	6.7A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	12A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full Load Runtime (min.)	8 min. (705w)
Half Load Runtime (min.)	23 min. (355w)
DC System Voltage (VDC)	18



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	<a href="#">RBC52</a> (quantity 3)
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	11.8 x 7.2 x 7.2
UPS Power Module Dimensions (hwd, cm)	29.8 x 18.4 x 18.4
UPS Power Module Weight (lbs.)	29
UPS Power Module Weight (kg)	13.2
UPS Shipping Dimensions (hwd / in.)	15 x 10.8 x 11.2
UPS Shipping Dimensions (hwd / cm)	38.1 x 27.3 x 28.6



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (lbs.)	31
Shipping Weight (kg)	14.1
UPS Housing Material	Polycarbonate
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	99.9
Battery Mode BTU / Hr. (Full Load)	326.9
AC Mode Efficiency Rating (100% Load)	96%
<b>COMMUNICATIONS</b>	
Communications Interface	USB
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="#">Ultimate Lifetime Insurance</a>
---	---

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.