

TAA-Compliant SmartPro 100/110/120V 1.05kVA 650W Line-Interactive Sine Wave UPS, SNMP, Webcard, Tower, USB, DB9 Serial

MODEL NUMBER: **SMART1050SLTAA**



Description

The SMART1050SLTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. 1050VA line-interactive tower UPS system for server, networking and telecommunications equipment. Upright tower form factor. Offers sine wave 100V, 110V or 120V nominal output in both AC and battery modes. Switches to battery-derived AC output during power failures and extreme voltage variations. Line-interactive automatic voltage regulation (AVR) provides voltage boost during brownouts and voltage cut during overvoltages to maintain regulated 100V, 110V or 120V nominal output over an input voltage range of 95-145V. Features NEMA 5-15P input plug and 8 NEMA 5-15R output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. HID-compliant USB port enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Features 3-stage metered current monitoring and battery charge status LEDs. Dataline surge suppression for dialup, DSL or network Ethernet connection. Utility power and voltage regulation LEDs. Audible alarm. Self-test. Field replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- SmartPro line-interactive UPS system is ideal for voice, data, medical and industrial networking applications
- Line-interactive automatic voltage regulation (AVR) maintains selectable 100V, 110V or 120V nominal output during brownouts as low as 83V and overvoltages to 145V
- Enables continuous operation through blackouts, voltage fluctuations and surges
- Line-interactive AVR provides a 14% boost during brownouts and a 12% voltage cut during overvoltages
- Standard internal battery set offers 19 min. runtime at half load (325W) and 7 min. at full load (650W)
- Space-saving upright tower format
- Network interfaces support simultaneous communications via built-in USB port, DB9 serial port and SNMPWEBCARD slot
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X.

Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 1.05kVA / 1050VA line interactive tower UPS, Sine wave output
- 100/110/120V nominal output during brownouts and overvoltages
- USB, RS232 and slot for optional SNMP/Web card
- Detailed status LEDs, Single line TEL / DSL surge suppression
- NEMA 5-15P input, 8 NEMA 5-15R outlets

Package Includes

- SMART1050SLTAA TAA Compliant UPS System
- PowerAlert Software CD
- USB and serial cabling
- Owner's manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, timed inverter sutoff, activate self-test and output power control
- NEMA 5-15P input plug; 8 x battery-supported NEMA 5-15R output receptacles
- Front panel LEDs offer current monitoring, voltage regulation and battery charge level information
- UPS ships fully assembled in full compliance with DOT regulations; no time-consuming connection of internal batteries by user required
- Single-line tel/DSL or network Ethernet line surge suppression
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1050
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	650
Power Factor	0.6
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Nominal Voltage Details	120V default (voltage selection via back panel switches)
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	-13%, + 15%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(8) 5-15R
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	6.1A (120V), 6.6A (110V), 7.2A (100V)
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Full Load Runtime (min.)	7 min. (650w)
Half Load Runtime (min.)	19 min. (325w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	3 hours
Internal UPS Replacement Battery Cartridge	RBC24-SLT
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 95 to 145 (120v), 87 to 133 (110v), 83 to 121 (100v)
Overvoltage Correction	Voltage reduction of 12% applies when input is 127 to 145 (120v), 116 to 133 (110v), 111 to 121 (100v)
Undervoltage Correction	Voltage boost of 14% applies when input is 95 to 108 (120v), 87 to 99 (110v), 83 to 90 (100v)
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates power failure and overload conditions
LED Indicators	9 LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level
Site Wiring Fault Indication	Rear panel site wiring fault LED
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	690
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	10.2 x 6.8 x 13.2
UPS Power Module Dimensions (hwd, cm)	26 x 17.1 x 33.7
UPS Power Module Weight (lbs.)	36



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Power Module Weight (kg)	16.3
UPS Shipping Dimensions (hwd / in.)	14 x 9.8 x 18.5
UPS Shipping Dimensions (hwd / cm)	35.6 x 24.8 x 47
Shipping Weight (lbs.)	39.6
Shipping Weight (kg)	18
Cooling Method	Fan
UPS Housing Material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	141.1
Battery Mode BTU / Hr. (Full Load)	452.7
AC Mode Efficiency Rating (100% Load)	94%
Audible Noise	Audible Noise < 50 dBA at Front Side 1 Meter
COMMUNICATIONS	
Communications Interface	USB (HID enabled); DB9 Serial; Slot for SNMP/Web interface
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications.
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
LINE / BATTERY TRANSFER	
Transfer Time	4-6 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	95V (120V), 87V (110V), 83V (100V)
High Voltage Transfer to Battery Power (Setpoint)	145V (120V), 133V (110V), 121V (100V)
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.