

42U SmartRack Value Enclosure

MODEL NUMBER: **SR42UBEVS**



Description

SmartRack enclosures are designed for secure, high density server and networking applications in IT environments. Designed with provisions to integrate cooling, power distribution and cable management, SmartRack enclosures make ideal homes for mission-critical equipment. Tool-less mounting slots allow quick installation of PDUs and vertical cable managers. Adjustable mounting rails include an easy-view depth index to eliminate time-consuming measurements. Lightweight modular doors and side panels provide safe, convenient service access. Integrated latching tabs facilitate combining enclosures in rows for standard data center latching applications. SmartRack enclosures support cooling, cable management, power distribution and monitoring features that keep critical servers and network equipment operating nonstop.

Features

- **This product is not available for purchase in the United States or Canada.**
- Ships disassembled for easy transport
- Ships with flat front door, split rear doors, full length side panels and roof and bottom panels
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring time-consuming measurements.
- Toolless accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Maximum usable internal depth of 35 inches/889 mm (front to rear rail).
- Compatibility with airflow optimization accessories as well as cable management accessories.

Highlights

- Ships disassembled for easy transport
- 42U SmartRack enclosure with doors, side, roof and bottom panels
- 4 interior vertical posts with unthreaded square hole openings
- Standard 24" (600mm) width and 40" (997mm depth) for optimizing floor space
- Includes 50 pieces of M6 cage nuts and 50 pieces of M6 screws (equipment mounting hardware)
- **This product is not available for purchase in the United States or Canada.**

Package Includes

- (1) Front door
- (2) Rear door panels
- (2) Full-length side panels
- (1) Floor panel
- (1) Roof panel
- (4) Vertical mounting rails
- (2) Vertical cable managers
- (6) Side rails
- Owner's Manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| PHYSICAL | |
|---|----------------------------|
| Installed Whole System Maximum Rack Depth (in.) | 35 |
| Installed Whole System Maximum Rack Depth (cm) | 88.9 |
| Installed Whole System Minimum Rack Depth (in.) | 4 |
| Rack Height (U Spaces) | 42 |
| Shipping Dimensions (hwd / in.) | 80.62 x 17 x 28.25 |
| Shipping Dimensions (hwd / cm) | 204.77 x 43.18 x 71.75 |
| Shipping Weight (lbs.) | 290 |
| Shipping Weight (kg) | 132 |
| Unit Dimensions (hwd / in.) | 80.66 x 23.63 x 39.28 |
| Unit Weight (lbs.) | 227 |
| Unit Weight (kg) | 103 |
| Unit Dimensions (cm) | 204.8764 x 60.02 x 99.7712 |
| Color | Negro |
| Hinged (Swings Away from Wall Bracket) | No |
| CERTIFICATIONS | |
| Certifications | EIA-310-E |
| NOM (Mexico) | Tested to NOM (Mexico) |
| Approvals | UL60950; RoHS |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.