

VGA Coax Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M), 15-ft.

MODEL NUMBER: P502-015



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- Resolutions up to 2048 x 1536

System Requirements

 Monitor with removable HD15 cable or CPU to Splitter

Package Includes

 15-ft. SVGA/VGA Monitor Cable HD15M to HD15M Gold Connectors w/ RGB Coax

Description

Tripp Lite's 15-foot SVGA/VGA monitor replacement cable is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold-plated connectors and gold plated copper contacts ensure excellent conductivity.
- HD15 male to HD15 male molded connectors
- Resolutions up to 2048 x 1536

Specifications

OVERVIEW		
Chromebook Compatible	No No	
Style	Monitor Cables	
Model Type	VGA	
Cable Types	MONITOR	
INPUT		
Cable Length (ft.)	15	
Cable Length (m)	4.57	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL		
Color	Black	
CONNECTIONS		
Connector A	HD15 (MALE)	
Connector B	HD15 (MALE)	
CERTIFICATIONS		
Certifications	RoHS-Compliant	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.