

SmartRack 15U Wall-Mount Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW15US**



Highlights

- 15U with adjustable front and rear vertical rackmount rails
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Description

Tripp Lite's SRW15US Wall Mount Rack Enclosure Cabinet is the ideal storage solution for standard rackmount equipment in applications with limited floor space. Constructed with a hinged wall mounting bracket and a sturdy steel frame, it can accommodate up to 225 lbs. of equipment in 15U of rack space. Four adjustable vertical mounting rails with square holes accommodate all standard 19-inch rack equipment. To allow easy access to rackmounted equipment, the enclosure cabinet is hinged to swing away from the wall mounting bracket. The SRW15US also features perforated lockable side panels and front door, assuring generous airflow to keep equipment operating safely. The front door is reversible and the side panels are removable for easy access to equipment. The top and bottom panels of the enclosure include convenient cable routing ports.

Features

- 15U wall-mounted enclosure
- Adjustable mounting depths from 3" to 20.5" inches
- Ventilated front door and side panels for increased airflow
- Hinged cabinet swings away from wall bracket for easy equipment and cable access
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Package Includes

- SRW15US Wallmount Rack Enclosure
- (42) M6 screws
- (42) M6 cage nuts
- (42) M6 washers
- (2) Keys
- Owner's Manual

Specifications

OVERVIEW

| | |
|-------|--------------|
| Style | Wall Mounted |
|-------|--------------|



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| PHYSICAL | |
|---|---|
| Installed Whole System Maximum Rack Depth (in.) | 20.5 |
| Installed Whole System Maximum Rack Depth (cm) | 52.07 |
| Installed Whole System Minimum Rack Depth (in.) | 3 |
| Installed Whole System Minimum Rack Depth (cm) | 7.62 |
| Rack Height (U Spaces) | 15 |
| Shipping Dimensions (hwd / in.) | 33.07 x 26.38 x 24.41 |
| Shipping Dimensions (hwd / cm) | 84 x 67 x 62 |
| Shipping Weight (lbs.) | 96 |
| Shipping Weight (kg) | 43.5 |
| Unit Dimensions (hwd / in.) | 30.33 x 23.63 x 21.6 |
| Unit Weight (lbs.) | 88.2 |
| Unit Weight (kg) | 40 |
| Unit Dimensions (cm) | EXTERNAL DIMENSIONS: 77 x 60 x 54.9 (HWD) |
| Color | Black |
| Weight Capacity - Stationary (lbs.) | 225 |
| Weight Capacity - Stationary (kg) | 102.1 |
| Factory Preset Rack Depth (in.) | 10.42 |
| Factory Preset Rack Depth (cm) | 26.47 |
| Cable Access Hole Measurement (inches) | 9.812 x 2.35 (l x w) |
| Hinged (Swings Away from Wall Bracket) | Yes |
| SPECIAL FEATURES | |
| Grounding Lug | Front and Back door frames |
| CERTIFICATIONS | |
| NOM (Mexico) | Tested to NOM (Mexico) |
| Approvals | EIA-310-E, IEC 60297-3-100, DIN 41494, IP20 Protection Rating, RoHS |
| WARRANTY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|-------------------------|
| Product Warranty Period (Worldwide) | 5-year limited warranty |
|-------------------------------------|-------------------------|

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.