

VGA Coax Monitor Cable, High Resolution Cable with RGB Coax (HD15 M/M), 50-ft.

MODEL NUMBER: **P502-050**



Description

Tripp Lite's 50-foot SVGA/VGA Monitor Cable (Male-Male) is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold-plated connectors and gold-plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high-density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors
- Resolutions up to 2048 x 1536

Specifications

OVERVIEW	
Chromebook Compatible	No
Style	Monitor Cables
Model Type	VGA
Cable Types	MONITOR
INPUT	
Cable Length (ft.)	50
Cable Length (m)	15.24

Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- Resolutions up to 2048 x 1536

System Requirements

- Monitor with removable HD15 cable
- Switchbox w/HD15F to CPU w/HD15F

Package Includes

- VGA Monitor Cable HD15M to HD15M Gold Connectors w/ RGB Coax- 50ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.